

1		2		3		4																																																					
A		B		C		D																																																					
<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~068*1T~</td><td>GRAY</td></tr><tr><td>~068*2T~</td><td>BLACK</td></tr></tbody></table>								Part No.	Cable color	~068*1T~	GRAY	~068*2T~	BLACK																																														
Part No.	Cable color																																																										
~068*1T~	GRAY																																																										
~068*2T~	BLACK																																																										
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table> 3 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>500, the angle is optional. 4. Specifications are subject to change without notice.								Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%																																										
Length L [mm]	Tolerance [mm]																																																										
35 ≤ L ≤ 200	±4																																																										
200 < L ≤ 500	±8																																																										
500 < L ≤ 1000	±12																																																										
1000 < L	±1.5%																																																										
【 DIMENSIONS OF CONNECTOR 】																																																											
<table border="1"><thead><tr><th>1</th><th>U.FL-LP-068HF</th><th>CL331-0566-4</th><th>2</th><th>1.13 Dia. coaxial cable</th><th>HALOGEN FREE</th></tr><tr><th>NO.</th><th>PART NO.</th><th>CODE NO.</th><th>NO.</th><th>PART NO.</th><th></th></tr></thead><tbody><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr><tr><td colspan="2">APPROVED : TS. NOBE 18.06.19</td><td colspan="2">DRAWING NO.</td><td colspan="4">U.FL-2LPHF6-068**T-A-L 1</td></tr><tr><td colspan="2">CHECKED : MT. KANEKO 18.06.19</td><td colspan="2">PART NO.</td><td colspan="4"></td></tr><tr><td colspan="2">DESIGNED : MS. MATSUMOTO 18.06.19</td><td colspan="2">CODE NO.</td><td colspan="4"></td></tr><tr><td colspan="2">DRAWN : MS. MATSUMOTO 18.06.19</td><td colspan="2"></td><td colspan="4"></td></tr></tbody></table>								1	U.FL-LP-068HF	CL331-0566-4	2	1.13 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.		UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	APPROVED : TS. NOBE 18.06.19		DRAWING NO.		U.FL-2LPHF6-068**T-A-L 1				CHECKED : MT. KANEKO 18.06.19		PART NO.						DESIGNED : MS. MATSUMOTO 18.06.19		CODE NO.						DRAWN : MS. MATSUMOTO 18.06.19							
1	U.FL-LP-068HF	CL331-0566-4	2	1.13 Dia. coaxial cable	HALOGEN FREE																																																						
NO.	PART NO.	CODE NO.	NO.	PART NO.																																																							
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																																				
APPROVED : TS. NOBE 18.06.19		DRAWING NO.		U.FL-2LPHF6-068**T-A-L 1																																																							
CHECKED : MT. KANEKO 18.06.19		PART NO.																																																									
DESIGNED : MS. MATSUMOTO 18.06.19		CODE NO.																																																									
DRAWN : MS. MATSUMOTO 18.06.19																																																											
FORM HC0011-5-51 2 3 4																																																											



HIROSE
ELECTRIC
CO., LTD.

APPROVED : TS. NOBE 18.06.19
CHECKED : MT. KANEKO 18.06.19
DESIGNED : MS. MATSUMOTO 18.06.19
DRAWN : MS. MATSUMOTO 18.06.19

DRAWING
NO.
PART
NO.
CODE
NO.

U.FL-2LPHF6-068**T-A-L 1

1/1