



1		2		3		4																																																									
A		B		C		D																																																									
																																																															
				<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~062*1D~</td><td>GRAY</td></tr><tr><td>~062*2D~</td><td>BLACK</td></tr></tbody></table>				Part No.	Cable color	~062*1D~	GRAY	~062*2D~	BLACK																																																		
Part No.	Cable color																																																														
~062*1D~	GRAY																																																														
~062*2D~	BLACK																																																														
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table> 3 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>500, the angle is optional. 4. Specifications are subject to change without notice. 【 DIMENSIONS OF CONNECTOR 】 								Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%																																														
Length L [mm]	Tolerance [mm]																																																														
35 ≤ L ≤ 200	±4																																																														
200 < L ≤ 500	±8																																																														
500 < L ≤ 1000	±12																																																														
1000 < L	±1.5%																																																														
<table border="1"><thead><tr><th>1</th><th>U. FL-LP-062HF(06)</th><th>CL331-0561-0-06</th><th>2</th><th>0.95 Dia. coaxial cable</th><th colspan="3">HALOGEN FREE</th></tr><tr><th>NO.</th><th>PART NO.</th><th>CODE NO.</th><th>NO.</th><th>PART NO.</th><th colspan="3"></th></tr></thead><tbody><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr><tr><td colspan="2"> HIROSE ELECTRIC CO., LTD.</td><td>APPROVED : NK. NINOMIYA 18.06.22</td><td colspan="5">DRAWING NO. 1</td></tr><tr><td colspan="2"></td><td>CHECKED : MT. KANEKO 18.06.22</td><td colspan="5">PART NO. UFL-2LPHF6-062*D-A-L 1</td></tr><tr><td colspan="2"></td><td>DESIGNED : MS. MATSUMOTO 18.06.22</td><td colspan="5">CODE NO. 1/1</td></tr><tr><td colspan="2"></td><td>DRAWN : MS. MATSUMOTO 18.06.22</td><td colspan="5"></td></tr></tbody></table>								1	U. FL-LP-062HF(06)	CL331-0561-0-06	2	0.95 Dia. coaxial cable	HALOGEN FREE			NO.	PART NO.	CODE NO.	NO.	PART NO.				UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	 HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA 18.06.22	DRAWING NO. 1							CHECKED : MT. KANEKO 18.06.22	PART NO. UFL-2LPHF6-062*D-A-L 1							DESIGNED : MS. MATSUMOTO 18.06.22	CODE NO. 1/1							DRAWN : MS. MATSUMOTO 18.06.22					
1	U. FL-LP-062HF(06)	CL331-0561-0-06	2	0.95 Dia. coaxial cable	HALOGEN FREE																																																										
NO.	PART NO.	CODE NO.	NO.	PART NO.																																																											
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																																								
 HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA 18.06.22	DRAWING NO. 1																																																												
		CHECKED : MT. KANEKO 18.06.22	PART NO. UFL-2LPHF6-062*D-A-L 1																																																												
		DESIGNED : MS. MATSUMOTO 18.06.22	CODE NO. 1/1																																																												
		DRAWN : MS. MATSUMOTO 18.06.22																																																													
FORM HC0011-5-51																																																															