




Part No.	Cable color
~032*1TS~	White
~032*2TS~	Black

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 100$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	X.FL-LP-032(09)	CL331-0706-1-09	2	0.50 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003278	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18. 06. 22
HRS HIROSE ELECTRIC CO., LTD.			APPROVED : NK. NINOMIYA 16. 07. 23	DRAWING NO. X. FL-2LP9-032**TS-A-L 1		
			CHECKED : MT. KANEKO 16. 07. 23			
			DESIGNED : MS. MATSUMOTO 16. 07. 23			
			DRAWN : MS. MATSUMOTO 16. 07. 23			