

APPLICABLE STANDARD								
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ^{(1) (2)}		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽³⁾			
	VOLTAGE	60 V AC ⁽⁵⁾		OPERATING HUMIDITY RANGE	RH 85 % MAX ^{(2) (4)}			
	CURRENT	0.5 A ⁽⁵⁾		STORAGE HUMIDITY RANGE	RH 70 % MAX ^{(3) (4)}			
	APPLICABLE CABLE	AWG 36, 40 THIN COAXIAL CABLE						
SPECIFICATIONS								
ITEM		TEST METHOD		REQUIREMENTS		QT	AT	
CONSTRUCTION								
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×	
MARKING		CONFIRMED VISUALLY.				×	×	