SnapBee™

1.7mm pitch, Low Profile Wire-to-Board Connectors for Power Supplies

DF65 Series

(UL, C-UL, Listed)



■Features

1. Enhanced contact reliability and lock structure

The unique locking structure reinforces the engagement between the wire side portion and the header. This prevents the wire side from becoming misaligned due to stress from poorly routed wiring. (Fig.1) (Patented)

2. Vertical mating provides superior handling

The use of vertical mating style reduces assembly time and maximizes precious board space which gives designers more freedom when designing other components on the PCB. (Fig.2)

3. Highly reliable contact structure

The two point contact structure provides optimum reliability, a low mated height of 1.8mm and an effective mating length of 0.35mm.

4. Increased cable retention

The header is designed to press the terminal lance down during the mating operation; this prevents the lance from moving and enhances its strength.

5. High current of MAX 4A (24 AWG)

By utilizing highly conductive material for the female terminals and suppressing the contact resistance, the DF65 series can handle a maximum of 4A with 24 AWG wire.

6. Solder wicking prevention

Molding is done in a way that removes the gap between the contacts and the housing to prevent wicking.

7. Prevents Accidental unmating

The molded structure is designed to prevent accidental unmating due to poorly routed wiring and harsh loads.

8. UL and C-UL Certified

Lock structure and operation





Fig.1

Vertical mating provides superior operability and maximizes board space.



Fig.2

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

In cases where the application will demand a high level of reliability, such as automotive, please contact a company representative for further information.

■Product Specifications

Ratings	Current Rating	No. of Contacts	24 AWG	26 AWG	28 AWG	Operating Temperature Range	−40 to +105℃ (Note 2)
		3	4A/pin	2.5A/pin	2.5A/pin	Operating aHumidity Range	20 to 80% (Note 3)
		4				Storage Temperature Range	−10 to +60℃ (Note 4)
		5				Storage Humidity Range	40 to 70% (Note 4)
		6	3.5A/pin	2A/pin	2A/pin	UL/C-UL/File No. and Recognition No.	
		7				UL : E52653	
	Voltage Rating	Specification	AC/DC 50V			C-UL : E52653	

Item	Specifications	Conditions
1. Insulation resistance	100MΩ min.	Measured at DC 100V
2. Withstand voltage	No flashover or breakdown	AC 500V is applied for one minute.
3.Contact resistance	10mΩ max.	Measured at 1mA and no higher than 20mV
4. Vibration Resistance	No electrical discontinuity for more than 1μs	10 cycles in each of three directions at frequency 10-55 Hz, half amplitude 0.75mm
5. Shock Resistance	No electrical discontinuity for more than 1μs	Accelerated velocity : 490m/s^2, for 11 ms, half-sine in 3 directions, 3 times for each of the three directions
6. Moisture-resistance	Contact resistance : 20mΩ max. Insulation resistance : 500MΩ min.	Temperature : 40 ±2℃ ; humidity : 90 to 95%, left as it is for 96 hours
7. Temperature cycles	Contact resistance : 20mΩ max. Insulation resistance : 500MΩ min.	-55℃ : 30 minutes → 5 - 35℃ : 2 - 3 minutes → 85℃ : 30 minutes → 5 - 35℃ : 2 - 3 minutes) 5 cycles
8. Durability	Contact resistance : 20mΩ max.	Tin plated : 30 mating cycles Gold plated : 50 mating cycles
9. Resistance to solder heat	The resin components will not become deformed or lose performance due to deformities	Reflow : according to the recommended temperature profile Hand soldering : temperature of soldering iron at 350℃±10℃ for 3 seconds

Note 1 : This is the maximum current rating while all pins are powered or used as all power lines. Depending on pin assignment, more current may flow. When dividing the current more than the specified amount into multiple circuits, the actual current value may exceed the rated value. Please contact Hirose Electric, for inquiries on the assignment of pins and on the currents that can be delivered.
Note 2 : Includes the temperature rise of power lines.
Note 3 : Use without condensation on parts.
Note 4 : The storage condition refers to long-term storage of the product on the shelf before assembly. Please use the operating temperature for temporary storage such as pre-assembly and during shipping.
Note 5 : Information contained in this catalog represents general requirements for this Series. Please contact us for the drawings and specifications for a specific part number shown.

■Materials / Finish

Product	Part	Materials	Finish	UL specification	RoHS2
Header	Insulator	LCP	Black	UL94V-0	YES
	Contact	Brass	Tin Plated or Gold plated	–	
Crimp socket	Insulator	LCP	Beige	UL94V-0	
Crimp contact	Contact	Copper Alloy	Tin Plated or Gold plated	–	

■Product Number Structure

Refer to the chart below when determining the product specifications from the product number.
Please select from the product numbers listed in this catalog when placing orders.

●Header connector

DF 65 - ✻ P - 1.7 V
❶ ❷ ❸ ❹ ❺ ❻

❶Series Name : DF	❻Mounting style V : SMT Straight Type
❷Series No. : 65	
❸Number of contacts : 3, 4, 5, 6, 7	
❹Connector type P : Header	
❺Pitch : 1.7mm	

●Socket connector

DF 65 - ✻ S - 1.7 C
❶ ❷ ❸ ❹ ❺ ❻

❶Series Name : DF	❺Pitch : 1.7mm
❷Series No. : 65	❻Termination form C : crimp case
❸Number of contacts : 3, 4, 5, 6, 7	
❹Connector type S : socket	

●Crimp contact

DF 65 - 2428 SCF
❶ ❷

❶Applicable wire size 2428 : 24 to 28 AWG	❷Packaging style SCF : Socket contact･Reel･Tin plated SCFA : Socket contact･Reel･Gold plated

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

■Straight pin header



●Recommended PCB layout (t=1mm)



[Specification Number]**
(21) : Tin plated, embossed packaging
(78) : Gold plated, embossed packaging

Unit : mm

Part No.	HRS No.	No. of Contacts	A	B	C
DF65-3P-1.7V(**)	666-6004-5 **	3	7.5	3.4	6
DF65-4P-1.7V(**)	666-6006-0 **	4	9.2	5.1	7.7
DF65-5P-1.7V(**)	666-6001-7 **	5	10.9	6.8	9.4
DF65-6P-1.7V(**)	666-6008-6 **	6	12.6	8.5	11.1
DF65-7P-1.7V(**)	666-6014-9 **	7	14.3	10.2	12.8

Note 1 : This product is sold per reel with 4,000 connectors pcs/reel. Please order by reel quantities.
Note 2 : Please contact Hirose representative if you have request for (24) specification.

●Tape and Reel Dimensions



Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

■Crimp socket



Unit : mm

Part No.	HRS No.	No. of Contacts	A	B	C	D
DF65-3S-1.7C(**)	666-6005-8 **	3	6.13	5.2	7.8	3.4
DF65-4S-1.7C(**)	666-6007-3 **	4	7.83	6.9	9.5	5.1
DF65-5S-1.7C(**)	666-6002-0 **	5	9.53	8.6	11.2	6.8
DF65-6S-1.7C(**)	666-6009-9 **	6	11.23	10.3	12.9	8.5
DF65-7S-1.7C(**)	666-6015-1 **	7	12.93	12	14.6	10.2

[Specification Number]**
None : 1 package contains 100 pcs/pack

Note : Each package contains 100 pcs/pack. Please order in full package quantities.

◆Crimp contact



[Specification Number]**
None : 18,000 pcs/reel
(07) : 18,000 pcs/reel・Gold plated

Part No.	HRS No.	Description	Quantity	Finish
DF65-2428SCF	666-6003-2	Reel contact	18,000 pcs/reel	Tin plated
DF65-2428SCFA(**)	666-6016-4 **	Reel contact	18,000 pcs/reel	Gold plated

Note : This product is sold per reel (18,000 pcs/reel), please order by reel quantities.

● Applicable wire (Tinned, annealed copper wire)

Conductor size (Core structure)	Jacket Diameter
24 AWG (11 pieces/ϕ 0.16 mm)	ϕ1.11mm
26 AWG (7 pieces/ϕ 0.16 mm)	ϕ0.98mm
28 AWG (7pieces/ϕ 0.127 mm)	ϕ0.88mm

●Recommended wire
UL10368

●Strip length
1.4 to 1.8mm

Note : For applicable cable other than those listed above, refer to Crimp Condition Table. Crimp Condition Table is available on product web page.
(If you are using a cable that is not listed in Crimp Condition Table, please contact a Hirose sales representative.)

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

◆Tooling Information

Item	Part No.	HRS No.	Applicable contact
Applicator	AP105-DF65-2428S	901-4630-0	DF65-2428SCF, DF65-2428SCFA
Press body	CM-105C	901-0001-0	–
Hand tool	HT305/DF65-2428S (Note3)	550-0306-8	DF65-2428SCF, DF65-2428SCFA
Extraction tool	DF-C-PO (B)	550-0179-2	DF65-2428SCF

Note 1 : Hirose does not cover damage created by the use of unapproved Hirose Tools. Please contact your local Hirose Sales for clarification.
Note 2 : Please conduct crimping work according to the "Crimping work standards" and "Crimping condition table".
Note 3 : The compatible wire is limited to UL10368, 24 to 28 AWG.
Note 4 : When non-authorized tools are used, please consult with a Hirose sales representative regarding requests for the hand tool die drawing.

◆Precautionary notes

1. Recommended Soldering Profile (Compatible with lead-free soldering)	 **[Applicable Conditions]** 1. Peak temperature : MAX 250℃ 2. Heating Area : 220℃ or above, within 60sec . 3. Preheating Area : 150~180℃, 90~120sec. ∗ Measurement is conducted at the contact lead part Please check the mounting conditions before use, conditions such as solder paste types, manufacturer, PCB size and any other soldering materials may alter the performance of such materials. (Note 1) This temperature profile is a recommended value only ; please contact your Hirose Sales Rep for more information
2. Recommended hand soldering conditions	Temperature of soldering iron : 350±10℃, soldering time : no more than 3 seconds
3. Recommended screen thickness, aperture ratio (pattern surface ratio)	Thickness : 0.1mm, aperture opening ratio : 100%
4. Warping of PC Board	A maximum of 0.02mm at the center of connector, as measured from either end of the connector
5. Cleaning Conditions	IPA cleaning is allowed. (Cleaning is not recommended because cleaning may change the push/pull feeling etc. Please contact your local Hirose representative prior to the use of any cleaning agents.)
6. Precautions	■ When inserting the crimp contact into the crimp socket, do not insert it at a slanted angle to maintain the reliability of its performance. ■ Please use caution when mating/unmating this connector if it has not been mounted onto the PCB, doing so could deform or damage the contacts. ■ Do not pull on the wires of this connector as this may cause damage to the connector. ■ During the hand soldering process, make sure to not apply too much flux. Doing so may cause a solder wicking problem. ■ This product may experience some differences in color from one production lot to another. This color difference does not influence the performance of the connector. Black spots may appear on the mold resin but this does not affect the product quality.

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

7. Precautions	Please refer to the following documents. ■ Crimp Quality Standard (ETAD-H0733-00) ■ Cable Assembly Procedure (ETAD-H0736-00) ■ Mating/Unmating Operation Instruction Manual (ETAD-H0803-00) ■ Procedures for Using the Crimp Terminal Extracting Tool (ETAD-H0249-00) ■ Board-to-Wire Connector Guidelines (ETAD-H1023-00)
8. Mating and Unmating Operation	**Mating operation** ① Align the receptacle over the header  ② Insert and press down on the receptacle in the direction of the arrow.  ③ Completed mating operation  **Unmating operation** ① Start by lifting up on the front edge of the receptacle.  ② Pull it upward to release the friction fit lock portion.  ③ Reinforced lock portion will then be released. Continue lifting the receptacle in an upward direction. 

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

◆Crimping

■Items Required Prior to Starting

The work- related documents listed below are required before starting harness assembly.
(The ● mark indicates a required document.)
When the documents shown below are not available, ask a Hirose sales personnel to provide them.

Document Title	Description	Automatic Crimping Machine	Hand Crimping Tool	Remarks
(1) Main Unit of Crimping Machine Instruction Manual	Explanation of main press machine unit	●	–	Bundled with the purchase of the main press machine unit.
(2) Applicator Spare Parts Identification	Explanation for Applicator installation	●	–	Bundled with the purchase of applicator.
(3) Crimp Conditions	Standard values of : Crimp height, tensile strength	●	–	
(4) Crimp Quality Standards	Various standards for crimping conditions	●	–	
(5) Operating Instructions for Hand Tool	Inspection items of : Crimp height, tensile strength, other	–	●	Bundled with the purchase of hand tool.
(6) Cable Assembly Procedure	Cable assembly procedure	●	●	Ask a HRS sales representative.

■Tools

Use tools designated by Hirose when crimping.
・Crimping performed using tools other than those specified is outside the scope of warranty.
・The operating instructions manual is available for the crimping machine and the applicator. Be sure to carefully read the operating instructions manual before implementing the work.

■Applicable Electric Wires

For applicable cable other than those listed above, refer to Crimp Condition Table. Crimp Condition Table is available on product web page.
(If you are using a cable that is not listed in Crimp Condition Table, please contact a Hirose sales representative.)

[Precautions]
・Electric wires that are suitable for crimping connectors are tin-plated stranded soft copper wire.
・Avoid crimping solid wires, wires with polyester threads or tin-coated wires.
・Avoid crimping two electric wires together.
・The crimp height setting value (Note) may vary between tin-plated and gold- plated contacts even if the same electric wires are used.
・The crimp height setting value (Note) may vary depending on the difference in the core wire configuration even if the computed cross-sectional area is the same.

Note : The crimp height is an important item that determines crimping quality. We execute crimping tests for each electric wire to ensure the optimal value for the crimp height with high precision, thereby ensuring optimal setup values.

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

HIROSE ELECTRIC CO.,LTD.
2-6-3,Nakagawa Chuoh,Tsuzuki-Ku,Yokohama-Shi 224-8540,JAPAN
https://www.hirose.com/