

P= 0.5mm



Front Flip



Space Saving



### Features

- 1 Space-saving**  
- 0.5mm Pitch, 2.1mm Height,  
4.2mm Mounting Depth
- 2 User-Friendly design**  
- Clear tactile click
- 3 High reliability**  
- Enhanced contact reliability by 2-point contact  
- High FPC retention force with FPC side-catcher design

### Dimensions (50pos.)

### 2-point Contact Design

### Specifications



**Contact Points**

Enhanced contact reliability  
by 2-point contact design

Contact Resistance <sup>*1</sup>	50mΩ Max.
Withstanding Voltage	250V AC for 1 min.
Insulation Resistance	500MΩ Min.(500V DC)
Rated Current	0.5A
Rated Voltage	50V AC/DC
FPC Thickness	0.3±0.03mm

• RoHS compliant, Halogen-free product <sup>\*2</sup>

<sup>\*1</sup> FPC resistance is included.

<sup>\*2</sup> This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1,500ppm maximum total of chlorine and bromine.