

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△						△						
△						△						
APPLICABLE STANDARD												
RATING	OPERATING TEMPERATURE RANGE		-25 °C TO +85 °C			STORAGE TEMPERATURE RANGE		-10 °C TO +60 °C				
	VOLTAGE		AC 30 V , DC 42 V			APPLICABLE CABLE		(φ4)				
	CURRENT		5 A (USED AWG#18)									
		3 A (USED AWG#20~22)										
SPECIFICATIONS												
ITEM		TEST METHOD				REQUIREMENTS				QT	AT	
CONSTRUCTION												
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.				○	○	
MARKING		CONFIRMED VISUALLY.								○	○	
ELECTRIC CHARACTERISTICS												
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A				30 mΩ MAX.				○	—	
		CONTACT SHALL BE MEASURED AT DC — A				— mΩ MAX.				—	—	
INSULATION RESISTANCE		100 V DC.				1000 MΩ MIN.				○	—	
VOLTAGE PROOF		150 V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN.				○	—	
MECHANICAL CHARACTERISTICS												
CONNECTOR INSERTION AND WITHDRAWAL FORCES		0.67 ⁰ _{-0.003} BY STEEL GAUGE				INSERTION FORCES AND WITHDRAWAL FORCES : 0.15 N MIN				○	—	
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR. LOCKING DEVICE WITH LOOK.				INSERTION FORCES : 30N MAX WITHDRAWAL FORCES : 9 N MIN				○	—	
MECHANICAL OPERATION		5000 TIMES INSERTIONS AND EXTRACTIONS.				CONTACT RESISTANCE: 60 mΩ MAX				○	—	
VIBRATION		FREQUENCY 10 TO 55 Hz SINGLE AMPLITUDE 0.75 mm — m/s ² AT 2 h, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.				○	—	
SHOCK		490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTION				① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.				○	—	
CONTACT RETENTION FORCE		APPLYING A PULL FORCE THE WIRE AFTER THE THE APPLICABLE CRIMPED CONTACT IS ASSEMBLED WITH THE BODY.				20 N MIN				○	—	
ENVIRONMENTAL CHARACTERISTICS												
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.				① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				○	—	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → R/T → +85 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES. (R/T: ROOM TEMPERATURE)				① INSULATION RESISTANCE: 100 MΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				○	—	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.				NO HEAVY CORROSIN.				○	—	
DRY HEAT		EXPOSED AT + 85 °C , 96 h.				NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				○	—	
COLD		EXPOSED AT - 55 °C , 96 h.				NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				○	—	
REMARKS						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED		
(1) ABOVE SPECIFICATIONS SHOWS THE VALUE IN ASSEMBLED CONDITION WITH APPLICABLE CRAMP CONTACT.						D. Motome	D. Motome	E. Kuniu	M. Sato			
Unless otherwise specified, refer to JIS C 5042.						'05.11.11	'05.11.11	'05.11.11	'05.11.11			
Note QT:Qualification Test AT:Assurance Test O:Applicable Test												
HRS		HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET		PART NO. RP34L-5PA-3SC(71)				
CODE NO. (OLD) CL		DRAWING NO. ELC4-113158-71				CODE NO. CL 113-5178-4-71				1	1	