









May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1	2	3	4				
A				A			
B				B			
C				C			
D				D			
E				E			
<p>Notes</p> <p>1 This product is delivered disassembled.</p> <p>2 The recommended clamp torque of Ref.No.① to be 2 to 2.5N・m. LOCTITE 263, Henkel Japan or equivalent is recommended to prevent Ref.No.① from loosening.</p> <p>3 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. please before the use.</p>							
2	POLYPHENYLENE SULFIDE	(BLACK)	UL94V-0				
1	BRASS	BLACK CROME PLATING	3	ACRYLONITRILE BUTADIENE RUBBER (GRAY)			
NO.	MATERIAL	FINISH . REMARKS		NO. MATERIAL FINISH . REMARKS			
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED	HY. KOBAYASHI	18. 02. 26	DRAWING NO. EDC-110619-31-00		
		CHECKED	HY. KOBAYASHI	18. 02. 26	PART NO. JR13WCCA-5(31)		
		DESIGNED	TH. KAMEYA	18. 02. 24	CODE NO. CL114-2070-8-31		
		DRAWN	MK. INOUE	18. 02. 14	 1/1		
FORM HC0011-5-51		2	3	4			