





	Contact name	AWG No.	UL	CSA	TÜV	Contact No.
Operating temperature range	—	—	-10 ~ +60℃			—
Rated voltage	—	—	AC250V		AC250V	1.9
					AC125V	2~8, 10~16
Rated current	QR/P1-PC1B-※21	#14	10A	10A	10A	1.9
		#16		8A		
	QR/P1-PC1A-※11	#18	5A	5A	5A	
		#20	3A	3A	2.5A	
		#22~24			1A	
	QR/P1-PC2A-※11	#24	1A	2A	1A	
		#26		1A		
		#28		—		

※: 1 is a loose piece contact
※: 2 is a strip contact



- Notes
- 1 The dimensional tolerance of each contact hole position to be ± 0.1 .
 - 2 The dimensions in parentheses are for reference.
 - 3 Operating temperature range, rated voltage and rated current are per Table-1.
4. Directions for use.
- (1) Please do not use for the purpose of interrupting the current.
 - (2) Please use inside the enclosure or equipment.

1	PBT	Black , UL94V-0						
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED :TU. TANIGUCHI		20181205	DRAWING NO.	EDC-042994-21-00		
		CHECKED :TU. TANIGUCHI		20181205	PART NO.	QR/P6-16P-C(21)		
		DESIGNED :TS. ITO		20181205	CODE NO.	CL221-0207-6-21		
		DRAWN :SJ. SATO		20181204	 			