

Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




TABLE-1

APPLICABLE CABLE		
	INSULATION (Ømm)	0.90~1.00
	VINYL SHEATH (Ømm)	(4.8) ※1
	CONDUCTOR	AWG26
	SHIELD	BRAIDED SHIELD

NOTES: 1. () INDICATES THE REFERENCE DIMENSIONS.
 2. APPLICABLE CABLE DIMENSIONS AS SHOWN IN TABLE-1.
 ※1 THIS IS FOR REFERENCE.
 (DIMENSION VARIES ACCORDING TO JACKET HARDNESS.)
 3. PLEASE USE ACCESSORY AS A GUIDE PLATE AND ASSEMBLE CONNECTOR WITH CABLES INSERTING ACCESSORY INTO CONNECTOR.

2	PHOSPHOR BRONZE	CONTACT PLATING UNDER PLATING	GOLD 1.27µm NICKEL 2µm	4	POLYCARBONATE	TRANSPARENCY
1	POLYCARBONATE	TRANSPARENCY		3	BRASS	TIN PLATING 1µm
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS
UNITS		SCALE	COUNT	DESCRIPTION OF REVISIONS		DESIGNED
mm		4 : 1	△			CHECKED
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	:RI. TAKAYASU	15.04.15	DRAWING NO. EDC-041197-51-00	
		CHECKED	:RI. TAKAYASU	15.04.15	PART NO. TM11P-66P(51)	
		DESIGNED	:TS. ITO	15.04.14	CODE NO. CL222-2149-9-51	
		DRAWN	:TS. ITO	15.04.14	1/1	