



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES) 1. PARTS ①⑧⑨ ARE DELIVERED ASSEMBLED.
PARTS ②③④⑤⑥⑦ ARE DELIVERED DISASSEMBLED.
2. OUTER DIAMETER OF APPLICABLE CABLE IS $\phi 6.2 \pm 0.3$.
3. DIMENSIONS IN PARENTHESES ARE SHOWN AS REFERENCES.

4	STEEL	SURFACE PLATING : NICKEL 3μm MIN. UNDER PLATING : COPPER 2μm MIN.	9	STAINLESS STEEL				
3	STEEL	SURFACE PLATING : NICKEL 3μm MIN. UNDER PLATING : COPPER 2μm MIN.	8	STEEL	SURFACE PLATING : NICKEL 2μm MIN. UNDER PLATING : COPPER 1μm MIN.			
2	POLYCARBONATE	(GRAY), UL94V-0	7	BRASS				
1	POLYCARBONATE	(GRAY), UL94V-0	6	BRASS				
			5	STEEL	NICKEL PLATING : 3μm MIN.			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS			
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : YH. ENAMI	09. 12. 17	DRAWING NO.	EDC3-120648-01			
		CHECKED : HO. MIWA	09. 12. 17	PART NO.	FI-20-CV7			
		DESIGNED : HN. ANDO	09. 12. 17	CODE NO.	CL230-0525-2-00			
		DRAWN : HN. ANDO	09. 12. 17	 1/1				