


Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	 CABLE DIAMETER : φ5.1~7.1	
	VOLTAGE		CURRENT		
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-E-00003216	KN. ICHIKAWA	TU. TANIGUCHI	20201019
REMARK			APPROVED	A0. SUZUKI	20090416
THIS PRODUCT SHALL BE MATED WITH DH40-17S OR DH3*B-17S, IT APPLIES TO DH40-17S OR DH3*B-17S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS. Unless otherwise specified, refer to IEC 60512.			CHECKED	MO. SHIMOYAMA	20090416
			DESIGNED	TS. ITO	20090416
			DRAWN	TS. ITO	20090416
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test		
	SPECIFICATION SHEET		PART NO.	DH-17-CV1B	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0009-6-00	 1/1