


Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	 CABLE DIAMETER : φ6.4~7.8
	VOLTAGE			
	CURRENT			


SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION


GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

--	--	--	--	--

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 1	DIS-E-00014810	KIM JAEHYEON	KG. OKITA	20230928

REMARK THIS PRODUCT SHALL BE MATED WITH DH40-27S OR DH3 * B-27S, IT APPLIES TO DH40-27S OR DH3 * B-27S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS. Unless otherwise specified, refer to IEC 60512.	APPROVED	KN. ICHIKAWA	20091117
	CHECKED	KN. ICHIKAWA	20091117
	DESIGNED	MO. SHIMOYAMA	20091117
	DRAWN	TM. ONO	20091117

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-126587-00-00
--	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	DH-27-CV1B	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0244-0010-5-00	 1/1