

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	 CABLE DIAMETER : φ7.3~9.3
	VOLTAGE			
	CURRENT			

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

--	--	--	--	--

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-E-00003216	KN. ICHIKAWA	TU. TANIGUCHI	20201019

REMARK THIS PRODUCT SHALL BE MATED WITH DH40-37S OR DH3 * B-37S, IT APPLIES TO DH40-37S OR DH3 * B-37S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS. Unless otherwise specified, refer to IEC 60512.	APPROVED	KN. ICHIKAWA	20091117
	CHECKED	KN. ICHIKAWA	20091117
	DESIGNED	MO. SHIMOYAMA	20091117
	DRAWN	TM. ONO	20091116

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-126588-00-00
--	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	DH-37-CV1B		
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL244-0011-8-00		1/1