

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85 % MAX	APPLICABLE CABLE	CABLE DIAMETER : ϕ8.8±0.5	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QTAT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	XX