


Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	 CABLE DIAMETER : φ5.1~7.1
	CURRENT		VOLTAGE	



### SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 2	DIS-E-00003216	KN. ICHIKAWA	TU. TANIGUCHI	20201019

REMARK THIS PRODUCT SHALL BE MATED WITH DH3 * B-17S, IT APPLIES TO DH3*B-17S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS. Unless otherwise specified, refer to IEC 60512. 	APPROVED	AO. SUZUKI	20090422
	CHECKED	KN. ICHIKAWA	20090422
	DESIGNED	MO. SHIMOYAMA	20090421
	DRAWN	MO. SHIMOYAMA	20090421

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-126852-00	
	SPECIFICATION SHEET	PART NO.	DH-17-CT1B	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL244-0039-7-00	 1/1