Sep.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.









Fig. 1 Reel drawing

HRS DRAWING FOR REFERENCE

Note:
1. Applicable wire is UL3266 AWG#24-#26.
   Insulation diameter ø1.49mm max.
2. Per reel : 10000 contacts.
3. Applicable crimping machine and crimping conditions (crimp height etc.)
   will be specified according to AWG # or wire applied.
4. Refer to ATAI-E3141 for crimp quality standards.
⚠1 5. For details of the packaging method of this product, refer to ETAP-E3151.

NO.	MATERIAL	FINISH . REMARKS
1	Copper alloy	Contact area : gold plating min. 0.2μm Terminal area : tin plating min. 0.5μm Others: nickel plating min. 0.5μm

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	10 : 1	⚠1	1	DIS-E-00013914	KG. OKITA	TU. TANIGUCHI	20230512

HIROSE ELECTRIC CO., LTD.

APPROVED	AH. KODAMA	20150721
CHECKED	AH. KODAMA	20150721
DESIGNED	KI. KAGOTANI	20150721
DRAWN	KI. KAGOTANI	20150721

DRAWING NO.	EDC-128586-00-00
PART NO.	MT50A-2426PCFA
CODE NO.	CL0248-0003-5-00 ⚠1 1/1