




Part No.	Cable color
~066*1~	GRAY
~066*2~	BLACK
~066*~	GRAY

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

[DIMENSIONS OF CONNECTOR]



For stable supply of this series,
material supplier of piece part#1
will be changed during 2019-2022.
Please note this change in advance.
There will be no difference in product
performance and quality.



2	E. FL CONTACT	CL331-0411-8-11		
1	E. FL-LP-066(01)	CL331-0402-7-01	3	1.32Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

UNITS mm		SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003764	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 20181217
APPROVED : NK. NINOMIYA 20180608				DRAWING NO.			
CHECKED : MT. KANEKO 20180608				PART NO.			
DESIGNED : MS. MATSUMOTO 20180608				CODE NO.			
DRAWN : MS. MATSUMOTO 20180608				E. FL-2LP-066*-A-L			

HRS HIROSE
ELECTRIC
CO., LTD.