



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1	2	3	4																																																			
A				A																																																		
B				B																																																		
C	<table border="1" data-bbox="1037 649 1348 784"><tr><th>Part No.</th><th>Cable color</th></tr><tr><td>~068*1T~</td><td>GRAY</td></tr><tr><td>~068*2T~</td><td>BLACK</td></tr></table>			Part No.	Cable color	~068*1T~	GRAY	~068*2T~	BLACK	C																																												
Part No.	Cable color																																																					
~068*1T~	GRAY																																																					
~068*2T~	BLACK																																																					
D	NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1" data-bbox="454 1041 1061 1243"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≦ L ≦ 200</td><td>±4</td></tr><tr><td>200 < L ≦ 500</td><td>±8</td></tr><tr><td>500 < L ≦ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table> 3. Specifications are subject to change without notice.			Length L [mm]	Tolerance [mm]	35 ≦ L ≦ 200	±4	200 < L ≦ 500	±8	500 < L ≦ 1000	±12	1000 < L	±1.5%	D																																								
Length L [mm]	Tolerance [mm]																																																					
35 ≦ L ≦ 200	±4																																																					
200 < L ≦ 500	±8																																																					
500 < L ≦ 1000	±12																																																					
1000 < L	±1.5%																																																					
E	【 DIMENSIONS OF CONNECTOR 】 			E																																																		
F	<table border="1" data-bbox="183 1870 1141 1948"><tr><td>1</td><td>U. FL-LP-068HF</td><td>CL331-0566-4</td><td>2</td><td>1.13 Dia. coaxial cable</td></tr><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td></tr></table> HALOGEN FREE <table border="1" data-bbox="183 1948 1516 2161"><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr><tr><td colspan="2"></td><td colspan="2">APPROVED : TS. NOBE 18. 06. 19</td><td colspan="4">DRAWING NO.</td></tr><tr><td colspan="2">HIROSE ELECTRIC CO., LTD.</td><td colspan="2">CHECKED : MT. KANEKO 18. 06. 19</td><td colspan="4">PART NO. U. FL-LPHF6-068**T-A-L 1</td></tr><tr><td colspan="2"></td><td colspan="2">DESIGNED : MS. MATSUMOTO 18. 06. 19</td><td colspan="4">CODE NO.</td></tr><tr><td colspan="2"></td><td colspan="2">DRAWN : MS. MATSUMOTO 18. 06. 19</td><td colspan="4"> 1 1</td></tr></table>			1	U. FL-LP-068HF	CL331-0566-4	2	1.13 Dia. coaxial cable	NO.	PART NO.	CODE NO.	NO.	PART NO.	UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE			APPROVED : TS. NOBE 18. 06. 19		DRAWING NO.				HIROSE ELECTRIC CO., LTD.		CHECKED : MT. KANEKO 18. 06. 19		PART NO. U. FL-LPHF6-068**T-A-L 1						DESIGNED : MS. MATSUMOTO 18. 06. 19		CODE NO.						DRAWN : MS. MATSUMOTO 18. 06. 19		1 1				F
1	U. FL-LP-068HF	CL331-0566-4	2	1.13 Dia. coaxial cable																																																		
NO.	PART NO.	CODE NO.	NO.	PART NO.																																																		
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																															
		APPROVED : TS. NOBE 18. 06. 19		DRAWING NO.																																																		
HIROSE ELECTRIC CO., LTD.		CHECKED : MT. KANEKO 18. 06. 19		PART NO. U. FL-LPHF6-068**T-A-L 1																																																		
		DESIGNED : MS. MATSUMOTO 18. 06. 19		CODE NO.																																																		
		DRAWN : MS. MATSUMOTO 18. 06. 19		1 1																																																		
FORM HC0011-5-51																																																						