

Part No.	Cable color.
~084N1~	White
~084N2~	Black
~084N4~	Blue


NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.

2 Tolerance for 【L】

Length L (mm)	Tolerance (mm)
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3. Specifications are subject to change without notice.


【 DIMENSIONS OF CONNECTOR 】



For stable supply of this series, material supplier of piece part#1 will be changed during 2019-2022. Please note this change in advance. There will be no difference in product performance and quality.

【 PRECAUTIONS FOR HANDLING 】

- ◆ Connector insertion and extraction
 - a. Connector shall be extracted vertically by specialised extraction JIG.
Part No.: H.FL-LP-NCCL Code: CL331-0551-7>
Never hold the cable when extracting the cable because it damages the connector.
 - b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.



1	H.FL75-LP(G)-084	CL331-0808-1	2	1.5 Dia. coaxial cable.
No.	Part No.	Code No.	No.	Part No.

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	•NK. NINOMIYA	20190425	DRAWING NO. EDC-384937-00-00	
		CHECKED	•NK. NINOMIYA	20190425	PART NO. H.FL75-LPG-084N*-A-L	
		DESIGNED	•MK. INOUE	20190425	CODE NO. CL321-5111-4-00	
		DRAWN	•MK. INOUE	20190425		