

Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK


NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.

2 Tolerance for [ L ]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$1000 < L$	$\pm 1.5\%$

3. Specifications are subject to change without notice.

#### 【 DIMENSIONS OF CONNECTOR 】



For stable supply of this series,  
material supplier of piece part#1  
will be changed during 2019-2022.  
Please note this change in advance.  
There will be no difference in product  
performance and quality.

1	W.FL-LP-040HF(06)	CL331-0563-6-06	2	0.81 Dia. coaxial cable	HALOGEN FREE					
NO.	PART NO.	CODE NO.	NO.	PART NO.						
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE			
<b>HRS</b> HIROSE ELECTRIC CO., LTD.		APPROVED	・NK. NINOMIYA	20181128	DRAWING NO.					
		CHECKED	・MT. KANEKO	20181128	PART NO.					
		DESIGNED	・MS. MATSUMOTO	20181128	CODE NO.					
		DRAWN	・MK. INOUE	20181128	NO.					
					WFL-LPHF6-04**TV-A-L			1		
									1	1