

1		2		3		4											
A		B		C		D											
		<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~044*1~</td><td>WHITE</td></tr><tr><td>~044*2~</td><td>BLACK</td></tr><tr><td>~044*4~</td><td>BLUE</td></tr></tbody></table>						Part No.	Cable color	~044*1~	WHITE	~044*2~	BLACK	~044*4~	BLUE		
Part No.	Cable color																
~044*1~	WHITE																
~044*2~	BLACK																
~044*4~	BLUE																
NOTE		① We indicate the length of the harness on the last of product name, 'L' part. ② Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table> ③ Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>150, the angle is optional. 4. Specifications are subject to change without notice.						Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%
Length L [mm]	Tolerance [mm]																
35 ≤ L ≤ 200	±4																
200 < L ≤ 500	±8																
500 < L ≤ 1000	±12																
1000 < L	±1.5%																
		【 DIMENSIONS OF CONNECTOR 】															
1		X.FL-LP-040		CL331-0700-5		2											
NO.		PART NO.		CODE NO.		NO.											
						0.64 Dia. coaxial cable											
						HALOGEN FREE											
UNITS mm				SCALE FREE		COUNT											
						DESCRIPTION OF REVISIONS											
						DESIGNED											
						CHECKED											
						DATE											
F		HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA 16. 07. 23		DRAWING NO.											
				CHECKED : MT. KANEKO 16. 07. 23		PART NO.											
				DESIGNED : MS. MATSUMOTO 16. 07. 23		X. FL-2LP-044**TS-A-L ①											
				DRAWN : MS. MATSUMOTO 16. 07. 23		CODE NO.											
						① 1 1											
FORM HC0011-5-51		2		3		4											