





Part No.	Cable color
~044*1~	WHITE
~044*2~	BLACK
~044*4~	BLUE

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 150$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	X.FL-LP-040	CL331-0700-5	2	0.64 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
			APPROVED : NK. NINOMIYA 16.07.23	DRAWING NO.		
			CHECKED : MT. KANEKO 16.07.23	PART NO.	X. FL-2LP-044**TS-A-L	1
			DESIGNED : MS. MATSUMOTO 16.07.23	CODE NO.		1/1
			DRAWN : MS. MATSUMOTO 16.07.23			