




Part No.	Cable color
~032*1~	WHITE
~032*2~	BLACK
~032*4~	BLUE

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 100$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	W.FL2-LP-032HF(06)	CL331-0340-1-06	2	0.50 Dia. coaxial cable	HALOGEN FREE		
NO.	PART NO.	CODE NO.	NO.	PART NO.			
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	·NK. NINOMIYA	16. 07. 28	DRAWING NO.		
		CHECKED	·MT. KANEKO	16. 07. 28	PART NO.		
		DESIGNED	·MS. MATSUMOTO	16. 07. 28	CODE NO.		
		DRAWN	·MS. MATSUMOTO	16. 07. 28	NO.		
WFL2-2LPHF6-032**TS-A-L					1		