


Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1	2	3	4																																																													
A				A																																																												
B				B																																																												
C	Product specification list			C																																																												
D	<table><tr><th>Part No.</th><th>CL code</th><th>Harness length (Unit:inch)</th><th>Harness length (Unit:mm)</th></tr><tr><td>HK-2P-MC1-A-4IN</td><td>CL321-1934-0-03</td><td>4±0.16</td><td>101.6±4</td></tr><tr><td>HK-2P-MC1-A-5IN</td><td>CL321-1934-0-04</td><td>5±0.16</td><td>127.0±4</td></tr><tr><td>HK-2P-MC1-A-6IN</td><td>CL321-1934-0-05</td><td>6±0.16</td><td>152.4±4</td></tr><tr><td>HK-2P-MC1-A-7IN</td><td>CL321-1934-0-06</td><td>7±0.16</td><td>177.8±4</td></tr><tr><td>HK-2P-MC1-A-8IN</td><td>CL321-1934-0-07</td><td>8±0.32</td><td>203.2±8</td></tr><tr><td>HK-2P-MC1-A-9IN</td><td>CL321-1934-0-08</td><td>9±0.32</td><td>228.6±8</td></tr><tr><td>HK-2P-MC1-A-10IN</td><td>CL321-1934-0-09</td><td>10±0.32</td><td>254.0±8</td></tr><tr><td>HK-2P-MC1-A-12IN</td><td>CL321-1934-0-10</td><td>12±0.32</td><td>304.8±8</td></tr><tr><td>HK-2P-MC1-A-18IN</td><td>CL321-1934-0-11</td><td>18±0.32</td><td>457.2±8</td></tr><tr><td>HK-2P-MC1-A-24IN</td><td>CL321-1934-0-12</td><td>24±0.48</td><td>609.6±12</td></tr><tr><td>HK-2P-MC1-A-36IN</td><td>CL321-1934-0-13</td><td>36±0.48</td><td>914.4±12</td></tr><tr><td>HK-2P-MC1-A-48IN</td><td>CL321-1934-0-14</td><td>48±0.71</td><td>1219.2±18</td></tr><tr><td>HK-2P-MC1-A-60IN</td><td>CL321-1934-0-15</td><td>60±0.87</td><td>1524.0±22</td></tr><tr><td>HK-2P-MC1-A-72IN</td><td>CL321-1934-0-16</td><td>72±1.07</td><td>1828.8±27</td></tr></table>			Part No.	CL code	Harness length (Unit:inch)	Harness length (Unit:mm)	HK-2P-MC1-A-4IN	CL321-1934-0-03	4±0.16	101.6±4	HK-2P-MC1-A-5IN	CL321-1934-0-04	5±0.16	127.0±4	HK-2P-MC1-A-6IN	CL321-1934-0-05	6±0.16	152.4±4	HK-2P-MC1-A-7IN	CL321-1934-0-06	7±0.16	177.8±4	HK-2P-MC1-A-8IN	CL321-1934-0-07	8±0.32	203.2±8	HK-2P-MC1-A-9IN	CL321-1934-0-08	9±0.32	228.6±8	HK-2P-MC1-A-10IN	CL321-1934-0-09	10±0.32	254.0±8	HK-2P-MC1-A-12IN	CL321-1934-0-10	12±0.32	304.8±8	HK-2P-MC1-A-18IN	CL321-1934-0-11	18±0.32	457.2±8	HK-2P-MC1-A-24IN	CL321-1934-0-12	24±0.48	609.6±12	HK-2P-MC1-A-36IN	CL321-1934-0-13	36±0.48	914.4±12	HK-2P-MC1-A-48IN	CL321-1934-0-14	48±0.71	1219.2±18	HK-2P-MC1-A-60IN	CL321-1934-0-15	60±0.87	1524.0±22	HK-2P-MC1-A-72IN	CL321-1934-0-16	72±1.07	1828.8±27	D
Part No.	CL code	Harness length (Unit:inch)	Harness length (Unit:mm)																																																													
HK-2P-MC1-A-4IN	CL321-1934-0-03	4±0.16	101.6±4																																																													
HK-2P-MC1-A-5IN	CL321-1934-0-04	5±0.16	127.0±4																																																													
HK-2P-MC1-A-6IN	CL321-1934-0-05	6±0.16	152.4±4																																																													
HK-2P-MC1-A-7IN	CL321-1934-0-06	7±0.16	177.8±4																																																													
HK-2P-MC1-A-8IN	CL321-1934-0-07	8±0.32	203.2±8																																																													
HK-2P-MC1-A-9IN	CL321-1934-0-08	9±0.32	228.6±8																																																													
HK-2P-MC1-A-10IN	CL321-1934-0-09	10±0.32	254.0±8																																																													
HK-2P-MC1-A-12IN	CL321-1934-0-10	12±0.32	304.8±8																																																													
HK-2P-MC1-A-18IN	CL321-1934-0-11	18±0.32	457.2±8																																																													
HK-2P-MC1-A-24IN	CL321-1934-0-12	24±0.48	609.6±12																																																													
HK-2P-MC1-A-36IN	CL321-1934-0-13	36±0.48	914.4±12																																																													
HK-2P-MC1-A-48IN	CL321-1934-0-14	48±0.71	1219.2±18																																																													
HK-2P-MC1-A-60IN	CL321-1934-0-15	60±0.87	1524.0±22																																																													
HK-2P-MC1-A-72IN	CL321-1934-0-16	72±1.07	1828.8±27																																																													
E				E																																																												
F	<table><tr><td>1</td><td>HK-P-SF085</td><td>CL338-0081-0-00</td><td>2</td><td>MCCA1/1</td><td>NISSEI ELECTRIC CO.,LTD.</td></tr><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td><td>MANUFACTURER</td></tr><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr><tr><td colspan="2"> HIROSE ELECTRIC CO., LTD.</td><td>APPROVED :AH. MARUYAMA 20210106</td><td colspan="4">DRAWING NO. ---</td></tr><tr><td colspan="2"></td><td>CHECKED :AH. MARUYAMA 20210106</td><td colspan="4">PART NO. HK-2P-MC1-A-*IN</td></tr><tr><td colspan="2"></td><td>DESIGNED :MS. MATSUMOTO 20210106</td><td colspan="4">CODE NO. ---</td></tr><tr><td colspan="2"></td><td>DRAWN :MS. MATSUMOTO 20210106</td><td colspan="4"></td></tr></table>			1	HK-P-SF085	CL338-0081-0-00	2	MCCA1/1	NISSEI ELECTRIC CO.,LTD.	NO.	PART NO.	CODE NO.	NO.	PART NO.	MANUFACTURER	UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	HIROSE ELECTRIC CO., LTD.		APPROVED :AH. MARUYAMA 20210106	DRAWING NO. ---						CHECKED :AH. MARUYAMA 20210106	PART NO. HK-2P-MC1-A-*IN						DESIGNED :MS. MATSUMOTO 20210106	CODE NO. ---						DRAWN :MS. MATSUMOTO 20210106					F												
1	HK-P-SF085	CL338-0081-0-00	2	MCCA1/1	NISSEI ELECTRIC CO.,LTD.																																																											
NO.	PART NO.	CODE NO.	NO.	PART NO.	MANUFACTURER																																																											
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																																									
HIROSE ELECTRIC CO., LTD.		APPROVED :AH. MARUYAMA 20210106	DRAWING NO. ---																																																													
		CHECKED :AH. MARUYAMA 20210106	PART NO. HK-2P-MC1-A-*IN																																																													
		DESIGNED :MS. MATSUMOTO 20210106	CODE NO. ---																																																													
		DRAWN :MS. MATSUMOTO 20210106																																																														
FORM HC0011-5-1		2	3	4																																																												