





2 Tolerance for [ L ]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$1000 < L$	$\pm 1.5\%$

4. Specifications are subject to change without notice.

### 【 DIMENSIONS OF CONNECTOR 】



1	X. FL-LP-040(C09)	CL331-0700-5-09		2	0.64 Dia. coaxial cable	HALOGEN FREE		
NO.	PART NO.	CODE NO.		NO.	PART NO.			
UNITS mm		SCALE FREE	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
			 2	DIS-D-00011688		MS. MATSUMOTO	MT. KANEKO	20220502
 HIROSE ELECTRIC CO., LTD.		APPROVED :NK. NINOMIYA		20200220	DRAWING NO.			
		CHECKED :MT. KANEKO		20200219	PART NO.			
		DESIGNED :MK. INOUE		20200219	X. FL-2LP9-044**TS-A-L			
		DRAWN :MK. INOUE		20200219	CODE NO.			
						