




1		2		3		4											
																	
<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~088*1T~</td><td>GRAY</td></tr><tr><td>~088*2T~</td><td>BLACK</td></tr></tbody></table>								Part No.	Cable color	~088*1T~	GRAY	~088*2T~	BLACK				
Part No.	Cable color																
~088*1T~	GRAY																
~088*2T~	BLACK																
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table> 3 Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional. 4. Specifications are subject to change without notice. 【 DIMENSIONS OF CONNECTOR 】 								Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$
Length L [mm]	Tolerance [mm]																
$35 \leq L \leq 200$	± 4																
$200 < L \leq 500$	± 8																
$500 < L \leq 1000$	± 12																
$1000 < L$	$\pm 1.5\%$																
1 U. FL-LP-088HF(06)		CL331-0560-8-06		2 1.37 Dia. coaxial cable		HALOGEN FREE											
NO.	PART NO.	CODE NO.		NO.	PART NO.												
UNITS mm		SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003261		DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18. 06. 21									
 HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA		16. 07. 25		DRAWING NO.		U. FL-2LPHF6-088**T-A-L 1									
		CHECKED : MT. KANEKO		16. 07. 25		PART NO.											
		DESIGNED : MS. MATSUMOTO		16. 07. 25		CODE NO.											
		DRAWN : MS. MATSUMOTO		16. 07. 25		NO.											
FORM HC0011-5-51		2		3		4											