

Part No.	Cable color
~068*1~	GRAY
~068*2~	BLACK
~068*3~	WHITE


NOTE 1 We indicate the length of the harness on the last of product name. 'L' part.

2 Tolerance for [ L ]

Length L [mm]	Tolerance [mm]
$100 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$L > 1000$	$\pm 1.5\%$

3. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	X.FL-LP(P)-068	CL331-0714-0	2	1.13 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm 	SCALE FREE 	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.	CHECKED : MT. KANEKO      20211027	DRAWING NO.		X.FL-LPP-068**T-A-L <span style="border: 1px solid black; padding: 0 2px;">1</span>		
	DESIGNED : MS. MATSUMOTO      20211027	PART NO.				
	DRAWN : MS. MATSUMOTO      20211027	CODE NO.				