




Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

NOTE We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 \leq L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

[DIMENSIONS OF CONNECTOR]



1	X. FL-LP-040	CL331-0700-5	2	0.81 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm		SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003337	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18.07.12
-------------	---	---------------	------------	--	---------------------------	-----------------------	------------------

 HIROSE ELECTRIC CO., LTD.	APPROVED	・NK. NINOMIYA	16. 07. 23	DRAWING NO.		
	CHECKED	・MT. KANEKO	16. 07. 23	PART NO.	X. FL-2LP-04**TV-A-L	1
	DESIGNED	・MS. MATSUMOTO	16. 07. 23	CODE NO.		1
	DRAWN	・MS. MATSUMOTO	16. 07. 23			

HRS HIROSE
ELECTRIC
CO., LTD.

DRAWING NO

X. FL-2LP-04**TV-A-L

PART	
NO	

NO.
CODE
NO.

$\triangle$	$\frac{1}{1}$
-------------	---------------