






PART No.	CODE No.	POS.	B	C	D
BM23PFO.8-10DS-0.35V(51)	-	10	4.25	1.40	2.84
BM23PFO.8-14DS-0.35V(51)	-	14	4.95	2.10	3.54
BM23PFO.8-20DS-0.35V(51)	-	20	6.00	3.15	4.59
BM23PFO.8-24DS-0.35V(51)	-	24	6.70	3.85	5.29
BM23PFO.8-30DS-0.35V(51)	-	30	7.75	4.90	6.34
BM23PFO.8-40DS-0.35V(51)	-	40	9.50	6.65	8.09
BM23PFO.8-42DS-0.35V(51)	-	42	9.85	7.00	8.44
BM23PFO.8-44DS-0.35V(51)	-	44	10.20	7.35	8.79
BM23PFO.8-46DS-0.35V(51)	-	46	10.55	7.70	9.14
BM23PFO.8-50DS-0.35V(51)	-	50	11.25	8.40	9.84
BM23PFO.8-54DS-0.35V(51)	-	54	11.95	9.10	10.54
BM23PFO.8-64DS-0.35V(51)	-	64	13.70	10.85	12.29

- NOTE
1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 2. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD $0.05 \mu m$ MIN.
SMT LEAD : GOLD $0.05 \mu m$ MIN.
UNDERPLATING : NICKEL $1 \mu m$ MIN.
(SURFACE : SEALING)
 3. METAL FITTING PLATING SPECIFICATIONS.
SMT LEAD : GOLD $0.05 \mu m$ MIN.
UNDERPLATING : NICKEL $1 \mu m$ MIN.
(SURFACE : SEALING)
 4. HRS MARK AND CAV NO. IS INDICATED IN APPROX POSITION SHOWN.

COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
2	RE-6-0742	LYJ	JHW		16.09.27						
3	RE-6-0806	MSH	JHW		17.01.05						
3	RE-6-1784	PSH	JHW		20.04.09						




ENGAGEMENT FIGURE (50:1)




4	PS	CLEAR (EMBOSSED CARRIER TAPE)						
3	 COOPER ALLOY			7	PS	CLEAR(REINFORCEMENT COLLAR)		
2	 COOPER ALLOY			6	PS	BLACK (PLASTIC REEL)		
1	LCP	UL94 V-0, BLACK		5	POLYESTER	CLEAR (COVER TAPE)		
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
				J. S. JANG 20.10.06	J. S. JANG 20.10.06	H. W. JO 20.10.06	H. W. JO 20.10.06	20.10.06
CODE NO. (COLD)		DRAWING NO.		PART NO.		BM23PFO.8-**-DS-0.35V(51)		
	SCALE	EDC3-*****						
	10:1							
UNITS		HIROSE KOREA CO.,LTD.		CODE NO		CL 66*-*****-51		1/3

6 RECOMMENDED PCB LAYOUT




RECOMMENDED METAL MASK DIMENSIONS METAL MASK THICKNESS : 100 μm



POS.	C	E
10	1.40	2.81
14	2.10	3.51
20	3.15	4.56
24	3.85	5.26
30	4.90	6.31
40	6.65	8.06
42	7.00	8.41
44	7.35	8.76
46	7.70	9.11
50	8.40	9.81
54	9.10	10.51
64	10.85	12.26

5 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.




REFLOW METHOD: N₂ REFLOW
 NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.
 1) REFLOW TIME
 DURATION ABOVE 220°C, 60 SEC MAX.
 (PEAK TEMPERATURE: 250°C MAX)
 2) PRE-HEAT TIME
 PRE-HEAT TEMPERATURE (MIN): 150°C
 PRE-HEAT TEMPERATURE (MAX): 180°C
 PRE-HEAT TIME: 90-120 SEC.

5. THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.
6. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.


DRAWING NO. EDC3-*****	PART NO. BM23PF0.8-***DS-0.35V(51)	SCALE 10:1	UNITS mm	HIROSE KOREA CO., LTD.	CODE NO CL 66***-***-51	2/3

EMBOSSED CARRIER TAPE PACKAGING (5:1)


STYLE AND DIMENTION OF REEL (FREE)




L-L (5:1)




N (10:1)




Part No. LABEL



Q-Q (FREE)



M-M (5:1)



DIRECTION OF UNREELING




POS.	F	G	H	J	K
10	16	7.5	4.36	17.5	21.5
14	16	7.5	5.06	17.5	21.5
20	16	7.5	6.11	17.5	21.5
24	16	7.5	6.81	17.5	21.5
30	16	7.5	7.86	17.5	21.5
40	24	11.5	9.61	25.5	29.5
42	24	11.5	9.96	25.5	29.5
44	24	11.5	10.31	25.5	29.5
46	24	11.5	10.66	25.5	29.5
50	24	11.5	11.36	25.5	29.5
54	24	11.5	12.06	25.5	29.5
64	24	11.5	13.81	25.5	29.5

DETAIL OF PART No. LABEL

SUPPLIER	
QUANTITY	
PART NO.	
CODE NO.	
DATE OF MANUFACTURED	
生産月日	年 月 日
図番	** ** *
品名	BM23PF0.8-**-DS-0.35V(51)
納入数量	10,000個
納入者	HIROSE KOREA

9 TAPING(FREE)



7 . PER REEL 10,000 CONNECTORS.

8 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

9 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

10 AFTER PACKAGING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET. AND TAPE DOWN AT THE END THE COLLAR.

	DRAWING NO.	EDC3-*****	PART NO.	BM23PF0.8-**-DS-0.35V(51)
	SCALE	10:1	CODE NO	CL 66**-*****-51
UNITS	HIROSE KOREA CO., LTD.			