










訂正事項		擔當	檢圖	年月日	訂正事項		擔當	檢圖	年月日
△數	DISCRPTION OF REVISIONS	B Y	CHKD	DATE	△數	DISCRPTION OF REVISIONS	B Y	CHKD	DATE
△				. .	△				. .
△				. .	△				. .
△				. .	△				. .



SECTION A-A



NOTE

1. LEAD CO-PLANARITY SHALL BE 0.1mmMAX
2. REEL : 1,500EA CONNECTORS
3. UL(File No. E132750) AUTHORIZATION ARTICLE.
C-UL(File No. E132750) AUTHORIZATION ARTICLE.



3	COPPER ALLOY	CONTACT AREA : GOLD 0.2 μ m MIN. SMT LEAD : GOLD 0.05 μ m MIN. UNDER PLATING : NICKEL 1 μ m MIN.		6	CONNECTOR	KW30-15S-1H	
2	PHOSPHOR BRONZE	Sn PLATED		5	PET	COVER TAPE	
1	LCP	UL94-V0, BLACK		4	PS	EMBOSS CARRIER TAPE	
NO.	MATERIAL	FINISH,REMARKS		NO.	MATERIAL	FINISH,REMARKS	
CODE NO. (OLD)				DRAWN		DESIGNED	
							
							
				DRAWING NO.		PART NO.	
SCALE				EDC3-633095		KW30-15S-1H (800)	
4:1							
UNITS				CODE NO		1	
mm				CL 6669-0016-0-800			
HRS HIROSE KOREA CO.,LTD.							