

A

B

C

D

E

F

1

2

3

4






5

6


7

8



訂正事項																	
△數	訂正事項				擔當	檢圖	年月日	△數	訂正事項				擔當	檢圖	年月日		
COUNT	DISCRIPTION OF REVISIONS				B	Y	CHKD	DATE	COUNT	DISCRIPTION OF REVISIONS				B	Y	CHKD	DATE
△								△									△
△								△									△
△								△									△
△								△									△



RECOMMENDED PCB LAYOUT (Top-View)



MATING FIGURE



NOTE

1. LEAD CO-PLANARITY SHALL BE 0.1mmMAX
2. 1REEL : 800EA CONNECTORS

3. UL(File No. E132750) AUTHORIZATION ARTICLE.
- C-UL(File No. E132750) AUTHORIZATION ARTICLE.



3	COPPER ALLOY	CONTACT AREA : GOLD 0.2㎛ MIN. SMT LEAD : GOLD 0.05㎛ MIN. UNDER PLATING : NICKEL 1㎛ MIN.	6	CONNECTOR	KW30-2S-2V		
2	PHOSPHOR BRONZE	Sn PLATED	5	PET	COVER TAPE		
1	LCP	UL94-V0, BLACK	4	PS	EMBOSS CARRIER TAPE		
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS		
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			CHOI 20.06.05 S.W	CHOI 20.06.05 S.W	LIM 20.06.12 S.M	LIM 20.06.12 S.M	
			DRAWING NO.		PART NO.		
SCALE 5:1			EDC3-633096		KW30-2S-2V (800)		
UNITS mm			HRS HIROSE KOREA CO.,LTD.		CODE NO		1/
					CL 6669-0017-3-800		