






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。

A
B
C
D
E
F




② かん合図

③ 2極

① (削除)

④ 推奨基板パターン図



- 注 1. リード平坦度は金具も含めて0.1以内。
② DF14-*S-1.25Cとのかん合長は7.3mm。(SMTリード部含まず)
③ 2極の簡易ロック穴は、図のようにセンターに1つとなります。
④ 推奨メタルマスク厚: 0.15mm
推奨メタルマスク開口率: 100%


△ (表中 2品目削除)

製品番号	製品コード	極数	A	B	C	D	E	F
DF14- 2P-1.25H(65)	CL538-0021-4-65	2	7.45	1.25	2.95	3.65	6.45	8.05
DF14- 4P-1.25H(65)	CL538-0023-0-65	4	9.95	3.75	5.45	6.15	8.95	10.55
DF14- 5P-1.25H(65)	CL538-0024-2-65	5	11.20	5.00	6.70	7.40	10.20	11.80
DF14- 6P-1.25H(65)	CL538-0025-5-65	6	12.45	6.25	7.95	8.65	11.45	13.05
DF14- 8P-1.25H(65)	CL538-0027-0-65	8	14.95	8.75	10.45	11.15	13.95	15.55
DF14- 9P-1.25H(65)	CL538-0028-3-65	9	16.20	10.00	11.70	12.40	15.20	16.80
DF14-10P-1.25H(65)	CL538-0029-6-65	10	17.45	11.25	12.95	13.65	16.45	18.05
DF14-15P-1.25H(65)	CL538-0084-4-65	15	23.70	17.50	19.20	19.90	22.70	24.30
DF14-20P-1.25H(65)	CL538-0089-8-65	20	29.95	23.75	25.45	26.15	28.95	30.55
DF14-25P-1.25H(65)	CL538-0094-8-65	25	36.20	30.00	31.70	32.40	35.20	36.80
DF14-30P-1.25H(65)	CL538-0020-1-65	30	42.45	36.25	37.95	38.65	41.45	43.05

2	黄銅	接触部 : 金めっき 0.1μm min	5	エラストマー	GREEN
		リード部 : すずめっき 1μm min	4	R. PVC	帯電防止処理, CLEAR
		下地 : ニッケルめっき 1μm min	3	りん青銅	すずめっき 1μm min
1	ポリアミド樹脂	BEIGE, UL94V-0			下地 : ニッケルめっき 1μm min
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
UNITS mm		SCALE 5 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-H-00007014	DESIGNED HK. HAYASHI
HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA	20200330	DRAWING NO.	ADC-160307-65-00
		CHECKED : TS. KUMAZAWA	20200330	PART NO.	DF14-*P-1.25H(65)
		DESIGNED : HK. HAYASHI	20200330	CODE NO.	CL538-
		DRAWN : DS. HIROWATARI	20200326		
					1/2

A
B
C
D
E
F

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。



DF 14-＊P-1.25H

HRS

ヒロセ電機

空チューブ回収に御協力下さい

1 2 3 4 5 6 7 8

A-A (10・1)

9.5±0.3

4.7±0.3

△1 (表中 2品目削除)

製品名	極数	入り数
DF14-2P-1.25H(65)	2	66
DF14-4P-1.25H(65)	4	49
DF14-5P-1.25H(65)	5	44
DF14-6P-1.25H(65)	6	39
DF14-8P-1.25H(65)	8	32
DF14-9P-1.25H(65)	9	30
DF14-10P-1.25H(65)	10	28
DF14-15P-1.25H(65)	15	20
DF14-20P-1.25H(65)	20	16
DF14-25P-1.25H(65)	25	13
DF14-30P-1.25H(65)	30	11

- 注5 付属品としてストッパーが2個付きます。
6 反り、曲がりとは510mmに対して2mm以内。
7 最小販売単位は表の数値になります。

HRS

DRAWING NO.	ADC-160307-65-00
PART NO.	DF14-＊P-1.25H(65)
CODE NO.	CL538-

△1 2/2