





RECOMMENDED LAND PATTERN DIMENSION OF PCB (MOUNTING SIDE)
(RECOMMENDED METAL MASK THICKNESS: 0.15mm)



A-A (10:1)



- NOTE
- 1 HRS MARK SHALL BE OPTIONAL.
 - 2 LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
 - 3 EMBOSSED CARRIER TAPE PACKAGING SHALL BE APPLIED FOR THIS PRODUCT.
SEE NEXT PAGE FOR DETAILS.
 - 4 THIS PRODUCT HAS TAPE FOR VACUUM PICKUP.
SEE NEXT PAGE FOR DETAIL OF STICKING POSITION, ETC.
 - 5 FOR MODIFICATION, ETC., PREVENTIVE HOLE FOR SINK MARK MAY BE ADDED ACCORDING TO CIRCUMSTANCES.
 - 6 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

2	PHOSPHOR BRONZE	CONTACT AREA: GOLD 0.1µm min.				
		LEAD AREA: TIN-PLATING 1µm min.				
		UNDER PLATING: NICKEL 2µm min.				
1	PPS	LIGHT BROWN UL94V-0	5	POLYIMIDE	TAPE FOR VUCUUM PICKUP	
			4	POLYESTER	TOP COVER TAPE	
			3	POLYSTYRENE	EMBOSSED CARRIER TAPE	
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS	
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS		
HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA	08.12.22	DRAWING NO.	EDC3-071640-23	
		CHECKED : HT. YAMAGUCHI	08.12.22	PART NO.	FX6-50S-0.8SV(93)	
		DESIGNED : SY. KAMIGA	08.12.19	CODE NO.	CL576-0104-6-93	
		DRAWN : TP. MATSUMOTO	08.12.19			