

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTES 3)	
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTES 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTES 2)(NOTES 3)	
	VOLTAGE		APPLICABLE CONNECTOR	DF81※-50S-0.4H(##)	
	CURRENT		APPLICABLE CABLE		
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT NOTE2: NON CONDENSING NOTE3: THE TERM "STORAGE" REFERS TO PRODUCTS STORED FOR A LONG PERIOD PRIOR TO MOUNTING AND USE. THE OPERATING TEMPERATURE AND HUMIDITY RANGE COVERS THE NON-CONDUCTING CONDITION OF CONNECTORS AFTER BOARD MOUNTING AND THE TEMPORARY STORAGE CONDITIONS OF TRANSPORTATION, etc Unless otherwise specified, refer to JIS C 5402,IEC60512.			APPROVED	TS. SAKATA	12. 09. 27
			CHECKED	HS. OZAWA	12. 09. 27
			DESIGNED	AH. MIYAZAKI	12. 09. 27
			DRAWN	AH. MIYAZAKI	12. 09. 27
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC4-345361-01	
HRS	SPECIFICATION SHEET		PART NO.	DF81-50P-LCH	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-8113-6-00	△ 1/1