

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO
PE

	COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	ELECTRIC SOURCE	PHASE	AC·DC	V	Hz	WEIGHT	5.0Kg				
	DISSIPATION POWER					APPLICABLE CONNECTOR	3840-1M-18P				
	AIR SOURCE					(CL238-2001-3)					
	AIR CONSUMPTION					APPLICABLE CABLE	φ 5.9CABLE (SWCC SHOWA DEVICE TECHNOLOGY CO., LTD.) IRV-28-18PS				
	OPERATING TEMPERATURE LIMIT	°C ~ °C				APPLICABLE EQUIPMENT	HANDPRESS OS-7				
SPECIFICATIONS											
	ITEM	TEST METHOD				REQUIREMENTS			QT	AT	
CONSTITUTION	APPEARANCE, STRUCTURE AND FINISH	Visually and by measuring instrument.				According to drawing.			○	○	
	MARKING	Confirmed visually.							○	○	
REMARKS						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
						Y. KUSABIRAKI 07.11.6	Y. KUSABIRAKI 07.11.6	S.TOYODA 07.11.15	S. Sakai 07.11.15		
Unless otherwise specified, refer to											
Note QT:Qualification Test AT:Assurance Test X:Applicable Test											
HRS		HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. 3840-1M/CK-MP		
CODE NO. (OLD)		DRAWING NO. ELC4-275916				CODE NO. CL902-2146-3			1/1		

