Rev.	Count	Description of rev.	BY	CHKD	Date	Rev.	Count	Description of rev.	BY	CHKD	Date
0	-	Released(RE-2-2883)	KYG	LHJ	25.08.21						
1	-	EC(RE-2-3009)	OSW	LHJ	26.04.15						
2	-	EC(RE-2-3012)	KYG	LHJ	26.05.14						

Applicable standard		-
Rating	Voltage	48V AC/DC
	Current	1.25A max. for each power pin (i.e., A1, A4, A9, A12, B1, B4, B5, B9, B12) 0.25A max. for the others.
Operating condition		-40℃~+105℃(Including temp. rise), 95% R.H. max.(Non-condensing)
Storage condition		-10℃~+60℃(With packing), 15%~70% R.H.

SPECIFICATIONS

No	TEST ITEM	TEST METHOD	TEST REQUIREMENT	QT	AT
CONSTRUCTION					
1	General examination	EIA 364-18 Visual inspection	No physical damage	O	O
ELECTRICAL CHARACTERISTICS					
2	Low level contact resistance	EIA 364-23 Measure at 20mV max open circuit at 100mA max. (DC or 1000Hz) 4-wire measurement is required and the resistance of PCB termination shall be deducted from the reading.	Initial : 40mΩ max After test : 50mΩ max	O	-
3	Dielectric withstanding voltage	EIA 364-20, Method B Measure with unmated condition. 100V AC RMS for 1 minute at sea level.	No disruptive discharge.	O	-
4	Insulation resistance	EIA 364-21 500V DC with unmated and mated condition.	100MΩ min.	O	-
5	Temperature rise	EIA-364-70, method B A current of 5.0 A shall be applied collectively to VBUS pins (i.e., pins A4, A9, B4, and B9) and 1.25 A applied to the Vconn pin (i.e., B5 of the plug connector) with the return path through the corresponding GND pins (i.e., pins A1, A12, B1, and B12). A minimum current of 0.25 A shall also be applied individually to all the other contacts.	Temperature rise shall not exceed 30℃ above the ambient temperature.	O	-

Remarks	Drawn	Designed	Checked	Approved	Release
	Y.G.KIM 25.08.21	Y.G.KIM 25.08.21	H.J.LEE 25.08.21	H.J.LEE 25.08.21	ENG 26.05.14 DEPT

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable

Drawing No.	CL No.	Part No.
ELC4-633754-02	CL ****-****-*-***	CX90MW9-24P*(002)

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

No	TEST ITEM	TEST METHOD	TEST REQUIREMENT	QT	AT
MECHANICAL CHARACTERISTICS					
6	Insertion force	EIA 364-13 Measure at 12.5mm/minute min.	Initial & after test : 5N～20N	O	-
7	Extraction force	EIA 364-13 Measure at 12.5mm/minute min.	Initial : 8N～20N After test : 6N～20N (with virgin plug)	O	-
8	Durability	EIA 364-09 Mated 10,000 times Mechanically operated : 500±50 cycles/hr Mating stroke : 2.75mm Insertion, extraction force shall be measured at a maximum speed of 12.5mm/min	No physical damage.	O	-
ENVIRONMENTAL CHARACTERISTICS					
9	Random vibration	EIA 364-28 Test condition VII, Test condition letter D Grms : 3.10g Frequency : 20～500Hz 15 minutes in each of 3 mutually perpendicular planes.	No physical damage. No discontinuity of over than 1μs.	O	-
10	Temperature life	EIA 364-17, Method A 105℃ without applied voltage for 120 hours.	No physical damage.	O	-
11	Cyclic temperature and humidity	EIA 364-31 25±3˚C/80±3% R.H. for 1 hour. 65±3˚C/50±3% R.H. for 1 hour. Ramp time : 0.5 hour Number of cycles : 24 cycles	No physical damage.	O	-
12	Thermal shock	EIA 364-32 10 cycles -55˚C and +105˚C	No physical damage.	O	-
13	Solderability	EIA 364-52 Dwell in 245±5℃ of the solder bath for 5 sec.	Solder coverage shall be 95% min. of the immersed surfaces.	O	-
14	Salt spray	EIA 364-26 5% of NaCl in 35℃ for 48 hours. Test with soldered condition on the PCB.	No corrosions that affect to the connector operation.	O	-
15	High temperature and humidity	EIA-364-31 High-temperature 85℃/85% R.H. for 120 hours.	No physical damage. No change to performance.	O	-
16	Mixed flowing gas	EIA 364-65 Measure Environment 30℃/70%R.H. Cl_2 10±3ppb, NO_2 200±50ppb, H_2S 10±5ppb, SO_2 100±20ppb Expose half of sample mated for 1/3 days and then unmated for 2/3 days .The others are exposed mated for full 7 days test period.	No corrosions that affect to the connector operation.	O	-

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable

Drawing No.	CL No.	Part No.
ELC4-633754-02	CL ****-****-*-***	CX90MW9-24P*(002)

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

No	TEST ITEM	TEST METHOD	TEST REQUIREMENT	QT	AT
17	Water resistance	Conduct the IP code test according to the corresponding P/N as shown as Table.1 ① IPX4 IEC60529 No matter which direction the water splashes on the enclosure, it must be waterproof. Duration : 10minutes at least. Water volume : 10L/min Pressure : 50~150 kPa ② IPX8 IEC60529 Immersion in the water at the depth of 1.5m for 30min	No water leakage.	O	-
18	Dust resistance	Conduct the IP code test according to the corresponding P/N as shown as Table.1 ① IP5X IEC60529 Duration : 8hours at least. Amount of talcum powder of the test chamber : 2kg/m^3 Dust type : Talcum Powder (less than 75μm) ② IP6X IEC60529 Duration : 8hours at least. Amount of talcum powder of the test chamber : 2kg/m^3 Dust type : Talcum Powder (less than 75μm)	① No ingress of dust to cause functional problems ② No ingress of dust	O	-
19	Reflow heat	Reflow profile Fig.1 Peak 250˚C max for 10 sec 2 times.	No deformation of mold No shape of blister and popcorn	O	-

REMARKS



[Fig.1] REFLOW TEMPERATURE

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable

Drawing No.	CL No.	Part No.
ELC4-633754-02	CL ****-****-*-***	CX90MW9-24P*(002)

Test Sequence Table

No	Test item	Test Group										
		A	B	C	D	E	F	G	H	I	J	K
1	General examination	1, 7	1, 15	1, 7	1, 7	1, 7	1, 3	1, 7	1, 7	1, 7	1, 4	1, 9
2	Low level contact resistance	3, 6	3, 14	3, 6	3, 6	3, 6		3, 6	3, 6	3, 6		3, 8
3	Dielectric withstanding voltage		4, 12									
4	Insulation resistance		5, 11									
5	Temperature rise										3	
6	Insertion force		6, 10									
7	Extraction force		7, 9									
8	Durability		8									4
9	Random vibration	4										
10	Temperature life			4								
11	Cyclic temperature and humidity				4							
12	Thermal shock					4						5
13	Solderability						2					
14	Salt spray							4				
15	High temperature and humidity								4			6
16	Mixed flowing gas									4		
17	Water resistance	5	13	5	5	5		5	5	5		
18	Dust resistance											7
19	Reflow heat	2	2	2	2	2		2	2	2	2	2

REMARKS

1) Numbers in the table above indicate the sequence corresponding to each test group.

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

[Table. 1] CX90MW9-24P*(002) Series P/N List

No.	P/N	Code No.	IP Code
1	CX90MW9-24P(002)	CL 6249-0010-7-002	IP54
2	CX90MW9-24P1(002)	CL 6249-0012-2-002	IP68

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.