




RJ-45



DIP



EMI Prevention




Features

- 1 Shield provides EMI prevention
- 2 Complies with US FCC Standard requirements
- 3 Space-saving 8 pin x 4-port type available
- 4 Compact with a mounted height of 11.9mm from the board surface, 14.6mm width and 17.6mm depth

Application Examples

- Industrial PC, LAN, HUB, Interphone, Computer, etc.



Product Number Structure

● Jack : TM11 R - 5L - 8 8
 1 2 3 4 5

1 Series Name	TM11 Series
2 Connector Type	R...Jack
3 Jack Type Number	3C ... Straight THT 5C ... Right Angle THT 5L ... Right Angle THT (Space-saving) 5N2 ... Right Angle THT (CAT.5 Compatible)
4 Jack Mating Port Size	6 ... 6 Contacts 8 ... 8 Contacts 32 ... 8 Contacts/4-port
5 No. of Inserted Contacts	6 ... 6 Contacts 8 ... 8 Contacts 32 ... 8 Contacts x 4-port = 32 Contacts

Specifications

Rated Current	0.5A
Rated Voltage	125V AC
Operating Temperature	-55 to +85°C*
Contact Resistance	230mΩ Max. (0.1A DC)
Withstanding Voltage	500V AC for 1 min.
Insulation Resistance	100MΩ Min. (100V DC)
Mating Durability	200 times

*Includes temperature rise due to current flow.

- RoHS compliant