Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard				
Rating	Operating temperature range	-40 ℃ to +90 ℃(90 %RH Max.)	Storage temperature range	-40 ℃ to +90 ℃(90 %RH Max.)
	Power	-- W	Characteristic impedance	50 Ω(0 to 12 GHz)
	Peculiarity	----	Applicable cable	1.13 Dia. coaxial cable.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
General examination	Visually and by measuring instrument.	According to drawing.	X	X
ELECTRICAL CHARACTERISTICS				
Insulation resistance	100 V DC.	500 MΩ Min.	X	X
Withstanding voltage	200 V AC for 1 min. current leakage 2 mA Max.	No breakdown. △1	X	X
Voltage standing wave ratio 〔1〕	Frequency 0 to 3 GHz. Frequency 3 to 6 GHz. Frequency 6 to 12 GHz.	VSWR 1.3 Max. VSWR 1.4 Max. VSWR 1.7 Max.	X	—
MECHANICAL CHARACTERISTICS				
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of 10 mm/min. and record the strength at which the cable or connector breaks.	9.8 N Min.	X	—

	Count	Description of revisions	Designed	Checked	Date
△1	2	DIS-D-00011712	MS. MATSUMOTO	MT. KANEKO	20220509

Remark HALOGEN FREE

Notes 〔1〕 VSWR is measured with SMA conversion adapters attached to both ends of the applicable cable assembled.

2. "L" at the end of the product name indicates the cable length (unit:mm).

3. Specifications are subject to change without notice.

Unless otherwise specified, refer to IEC 60512. △1

Approved	NK.NINOMIYA	20211027
Checked	MT.KANEKO	20211027
Designed	MS.MATSUMOTO	20211027
Drawn	MS.MATSUMOTO	20211027

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

		Drawing No.	
HRS	SPECIFICATION SHEET	Part No.	X.FL-LPP-068**T-A-L
	HIROSE ELECTRIC CO., LTD.	Code No.	△1 1/1

FORM HD0011-2-1