

A






B

C



D

E

F




SECTION A-A





訂正事項					訂正事項						
△數	DISCRIPTION OF REVISIONS	擔當	檢圖	年月日	△數	DISCRIPTION OF REVISIONS	擔當	檢圖	年月日		
COUNT		B	Y	CHKD	DATE	COUNT		B	Y	CHKD	DATE
△						△					
△						△					
△						△					
△						△					

RECOMMENDED PCB LAYOUT (Top-View)



MATING FIGURE



NOTE

1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX
2. 1 REEL : 1500EA CONNECTORS
3. UL (File No. E132750) AUTHORIZATION ARTICLE.
C-UL (File No. E132750) AUTHORIZATION ARTICLE.



2

3	COPPER ALLOY	CONTACT AREA : GOLD 0.2㎛ MIN. SMT LEAD : GOLD 0.05㎛ MIN. UNDER PLATING : NICKEL 1㎛ MIN.	6	CONNECTOR	KW30-10S-1H		
2	PHOSPHOR BRONZE	Sn PLATED	5	PET	COVER TAPE		
1	LCP	UL94-V0, BLACK	4	PS	EMBOSS CARRIER TAPE		
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS		
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			CHOI 20.06.15 S.W	CHOI 20.06.15 S.W	LIM 20.06.15 S.M	LIM 20.06.15 S.M	
		DRAWING NO.		PART NO.			
SCALE 4:1		EDC3-633094		KW30-10S-1H (800)			
UNITS mm		HRS HIROSE KOREA CO.,LTD.		CODE NO		CL 6669-0011-7-800	
						1/1	