


Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- △ Note 1. Applicable wire : 26 to 30 AWG
Outer diameter : ϕ 0.56 to 1.0mm
2. 1 reel:10000 contacts.
- ③ Style of reel and box are shown in figure.
- ① 4. A maximum of 5 reels are packed up in one box.
① 5. Please be sure to check the form of crimping using a cable when you adjust applicator.
① 6. Refer to the technical specification(ATAP-H0373-00)for the packing type.
① 7. Refer to the crimping quality standard(ETAD-H0953-00)for the packing type.

1	Phosphor bronze	Contact area:Gold plating 0.76 μ m Other:Nickel plating 0.5 μ m
---	-----------------	--

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 20:1	△の数 9	訂正記事 DIS-H-00004839	設計 HT. SATO
承認 : KJ. KATAYOSE 20050105			図番 : EDC-071220-05-03		
検 図 : TY. OMA 20050105			製品名 : DF13-2630SCFA(05)		
設 計 : TS. KUMAZAWA 20050105			製品コード : CL536-0298-5-05		
製 図 : TS. KUMAZAWA 20050105					