








Applicable standard					
Rating	Operating temperature range	-35 °C to +85 °C(Notes 1)	Storage temperature range	-10°C to +60 °C(Note 3)	
	Operating humidity range 	20% to + 80%(Note 2)	Storage humidity range	40% to + 70%(Note 3)	
	Voltage	150 V AC/DC	Current 	AWG 26 : 2.5A	
	Applicable cable	26 - 30 AWG		AWG 28 : 2.0A	
			AWG 30 : 1.0A		
Specifications					
Item	Test method	Requirements	QT	AT	
<b>Construction</b>					
General examination	Visually and by measuring instrument.	According to drawing.	X	X	
Marking	Confirmed visually.		X	X	
<b>Electric characteristics</b>					
Contact resistance Millivolt level method	20 mV MAX, 1mA (DC or 1000Hz).	30 mΩ MAX.	X	-	
<b>Mechanical characteristics</b>					
Contact insertion and extraction force	<input type="checkbox"/> 0.35±0.002mm by steel gauge.	Insertion force : 3.0N MAX. Extraction force : 0.3N MIN.	x	-	
Mechanical operation	50 times insertions and extractions.	① Contact resistance: 30 mΩ MAX. ② No damage, crack or looseness of parts.	X	-	
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 2 h, for 3 directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	-	
Shock	490 m/s <sup>2</sup> duration of pulse 11 ms at 3 times for 3 directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	-	
<b>Environmental characteristics</b>					
Rapid change of temperature 	Temperature -55→15 to 35 →+85→15 to 35 °c Time 30→10 to 15→ 30 →10 to 15min Under 5 cycles.	① Contact resistance: 30 mΩ MAX. ② No damage, crack or looseness of parts.	X	-	
Damp heat (Steady state)	Exposed at 40 ± 2 °c, 90 to 95 %, 96 h.	① Contact resistance: 30 mΩ MAX. ② No damage, crack or looseness of parts.	X	-	
<b>Remarks</b>					
Note 1: Include the temperature rising by current.					
Note 2: No condensing. 					
Note 3: Apply to the condition of long term storage for unused products before mounted on PCB. After mounted on PCB, operation temperature and humidity range is applied for interim storage during transportation.					
	Count	Description of revisions	Designed	Checked	Date
	4		HT. SATO	SZ. ONO	20190531
Unless otherwise specified , refer to IEC 60512.			Approved	KJ. KATAYOSE	20050105
			Checked	TY. OMA	20050105
			Designed	TS. KUMAZAWA	20050105
			Drawn	TS. KUMAZAWA	20050105
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing no.		ELC-071220-05-03
	Specification sheet		Part no.	DF13-2630SCFA (05)	
	Hirose electric co., ltd.		Code no.	CL536-0298-5-05	 1/1