




| CODE NO.        | CONTACT | A    | B    | C    | D    | E    | F    | G    | H    |
|-----------------|---------|------|------|------|------|------|------|------|------|
| CL683-0255-8-57 | 26      | 11.5 | 8.3  | 7    | 6    | 11.3 | 9.7  | 11.9 | 9.1  |
| CL683-0270-1-57 | 30      | 12.5 | 9.3  | 8    | 7    | 12.3 | 10.7 | 12.9 | 10.1 |
| CL683-0363-0-57 | 60      | 20   | 16.8 | 15.5 | 14.5 | 19.8 | 18.2 | 20.4 | 17.6 |
| CL683-0395-7-57 | 70      | 22.5 | 19.3 | 18   | 17   | 22.3 | 20.7 | 22.9 | 20.1 |
| CL683-0371-9-57 | 80      | 25   | 21.8 | 20.5 | 19.5 | 24.8 | 23.2 | 25.4 | 22.6 |

NOTES 1 : LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.

② IF THE RESIST PROCESSING HAS NOT MADE, IT HAS POSSIBILITY THAT THE TERMINAL TOUCHES WITH  AREA.  
PLEASE BE NOTED THIS POINT.

|     |                  |                                                                                                              |  |   |     |                              |                                                      |  |  |
|-----|------------------|--------------------------------------------------------------------------------------------------------------|--|---|-----|------------------------------|------------------------------------------------------|--|--|
|     |                  |                                                                                                              |  | 7 | PS  | CLEAR (REINFORCEMENT COLLAR) |                                                      |  |  |
|     |                  |                                                                                                              |  | 6 | PS  | BLACK (PLASTIC REEL)         |                                                      |  |  |
| 2   | POLYAMIDE (PA6T) | WHITE BEIGE , UL94V-0                                                                                        |  |   | 5   | POLYESTER                    | CLEAR (COVER TAPE)                                   |  |  |
| 1   | PHOSPHER BRONZE  | CONTACT AREA : GOLD PLATED 0.1μm min<br>LEAD AREA : GOLD PLATED 0.02μm min<br>UNDER PLATING : NICKEL 1μm min |  |   | 4   | PS                           | CLEAR (EMBOSSED CARRIER TAPE)                        |  |  |
|     |                  |                                                                                                              |  |   | 3   | PHOSPHER BRONZE              | TIN PLATED 1μm min<br>UNDER PLATING : NICKEL 1μm min |  |  |
| NO. | MATERIAL         | FINISH , REMARKS                                                                                             |  |   | NO. | MATERIAL                     | FINISH , REMARKS                                     |  |  |

|                           |  |                        |            |             |                              |  |          |         |      |
|---------------------------|--|------------------------|------------|-------------|------------------------------|--|----------|---------|------|
| UNITS<br>mm               |  | SCALE<br>5 : 1         |            | COUNT       | DESCRIPTION OF REVISIONS     |  | DESIGNED | CHECKED | DATE |
| HIROSE ELECTRIC CO., LTD. |  | APPROVED : KH. IKEDA   | 11. 12. 19 | DRAWING NO. | EDC3-162763-77               |  |          |         |      |
|                           |  | CHECKED : TS. MIYAZAKI | 11. 12. 19 | PART NO.    | DF17B(3. 0H) - *DS-0. 5V(57) |  |          |         |      |
|                           |  | DESIGNED : TR. YUNOKI  | 11. 12. 19 | CODE NO.    | CL683                        |  |          |         |      |
|                           |  | DRAWN : MS. SATO       | 11. 12. 19 |             |                              |  |          |         | 1/2  |
|                           |  |                        |            |             |                              |  |          |         |      |

