


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。

ELV, RoHS適合品



適合ケーブル径 :  $\phi 4.8 \sim 5.0$  mm

|                           |          |                       |              |                                            |          |                            |                           |                      |
|---------------------------|----------|-----------------------|--------------|--------------------------------------------|----------|----------------------------|---------------------------|----------------------|
| 1                         | 銅合金      | 錫めっき                  |              |                                            |          |                            |                           |                      |
| NO.                       | MATERIAL | FINISH                | REMARKS      | NO.                                        | MATERIAL | FINISH                     | REMARKS                   |                      |
| UNITS<br>mm               |          | SCALE<br>2:1          | COUNT<br>    | DESCRIPTION OF REVISIONS<br>DIS-T-00018495 |          | DESIGNED<br>KN. YANAGIMOTO | CHECKED<br>E.J. WAKATSUKI | DATE<br>2023. 07. 04 |
| HIROSE ELECTRIC CO., LTD. |          | APPROVED : NH. NAKATA | 2014. 03. 08 | DRAWING NO. ADC-353799-00-00               |          |                            |                           |                      |
|                           |          | CHECKED : TS. KUBOTA  | 2014. 03. 07 | PART NO. GT32-4DS-5CF                      |          |                            |                           |                      |
|                           |          | DESIGNED : NK. IKUTA  | 2014. 03. 07 | CODE NO. CL0782-0040-3-00                  |          |                            |                           |                      |
|                           |          | DRAWN : NK. IKUTA     | 2014. 03. 07 | 1/1                                        |          |                            |                           |                      |