Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.











Notes. 1. Recommended cable condition is shown below.
A list of copatible cables is available on the Hirose website.
When using a non-recommeded cable, please contact a Hirose sales representative.
For wiring and assembly procedures, please refer to technical specification (ATAD-E3256) for IX30G, IX31G, and IX32G, and to technical specification (ATAD-E3162) for IX35G.

Recommended Cable

Items		IX30G	IX31G	IX32G	IX35G
Conductor	Size	AWG26 to 28	AWG24 to 25	AWG22	AWG30
	Composition	7 stranded			
	Material	Annealed copper Wire			
Insulation O.D.		ø0.95 to 1.05mm	ø1.1 to 1.25mm	ø1.4 to 1.6mm	ø0.54 to 0.72mm
Braid Shield		Tin plating			
Sheath O.D.		ø6.3 to 7.2mm			



2. Type A and Type C are defined for 10/100 Mbit/s and 1/10 Gbit/s Ethenet communication.
Please use Type B for all othes non Ethernet applications like signaling, serial or other industrial bus communication systems. Type B is not defined pin assignment.

HRS DRAWING FOR REFERENCE

Pin Assignment For 10/100 Mbit/s And 1/10 Gbit/s Ethernet

Contact No.	Signal		Use TIA Cable	
	10/100Mbit/s	1/10Gbit/s	TIA/EIA-568-A	TIA/EIA-568-B
1	TX+	BI_DA+	White/Green	White/Orange
2	TX-	BI_DA-	Green	Orange
3	N.C	N.C	N.C	N.C
4	N.C	BI_DC+	Blue	Blue
5	N.C	BI_DC-	White/Blue	White/Blue
6	RX+	BI_DB+	White/Orange	White/Green
7	RX-	BI_DB-	Orange	Green
8	N.C	N.C	N.C	N.C
9	N.C	BI_DD+	White/Brown	White/Brown
10	N.C	BI_DD-	Brown	Brown

Mating Key

Type A



Type B



Type C



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
4	PA	30G : Black, UL94V-0 31G・32G : Gray, UL94V-0	7	Stainless Steel	Nickel 0.2 μm min
3	Stainless Steel		6	Stainless Steel	Nickel 1 μm min
2	PA	Black, UL94V-0	5	PC	30G : Clear, UL94V-0 31G : Clear yellow, UL94V-0 32G : Clear blue, UL94V-0 35G : Clear red, UL94V-0
1	銅合金	Contact area : Gold 0.2 μm min Wiring area : Gold 0.03 μm min Under plating : Nickel 2 μm min			

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2:1	△1	1	DIS-E-00021759	HR.SASAKI	KZ.KAI	2026.06.10

HIROSE ELECTRIC CO.,LTD.

APPROVED	TU.TANIGUCHI	2026.06.09
CHECKED	KZ.KAI	2026.06.09
DESIGNED	HN.SAITO	2026.06.09
DRAWN	HN.SAITO	2026.06.09

DRAWING NO.	EDCX-411766-00-00
PART NO.	IX3*G2-*-*S-CV(7.0)(06)
CODE NO.	CL251

△1 1/3

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

HRS DRAWING FOR REFERENCE

[3] Product Structure



[3] Shield Shell and Guide Delivery Form



Plug unit



Mated Condition



[3] This product is packaged separatly by the each parts.
The delivery condition of Shield shell and Guide are shown in "Shield Shell and Guide Delivery Form".

HRS	DRAWING NO.	EDCX-411766-00-00
	PART NO.	IX3*G2-*-*S-CV(7.0)(06)
	CODE NO.	CL251

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

4. Product Number Structure

IX 30G # - A - 10 S - CV (7.0) (##)
① ② ③ ④ ⑤⑥ ⑦ ⑧ ⑨

①Series Name	IX Series
②Assembly Method	30G : IDC (AWG#26 to 28, Insulator Outer Diameter ø0.95 to 1.05mm) 31G : IDC (AWG#24 to 25, Insulator Outer Diameter ø1.1 to 1.25mm) 32G : IDC (AWG#22, Insulator Outer Diameter ø1.4 to 1.6mm) 35G : IDC (AWG#30, Insulator Outer Diameter ø0.54 to 0.72mm)
③Version	Blank : Ver.1 2 : Ver.2
④Mating Key	A : Type A/For Ethenet B : Type B/For except Ethenet C : Type C/For Ethenet
⑤ Maximum Number of Usable Positions	10 : 10 pos. 8* : 8 pos.
⑥Contact Gender	S:Female Contact
⑦ Plug Cover Cabling Direction	CV : Straight CVL1 : Downward Cabling CVL2 : Upward Cabling
⑧ Applicable Cable Diameter	(7.0)** : Sheath Outer Diameter ϕ6.3 to 7.2mm Z : Sheath Outer Diameter ø6.3 to 7.2mm
⑨ Plating Specifications	(06) : Gold Plated (07) : Palladium-Nickel Plated+Gold Plated

* For IX32G, Contacts No.3 and 8 do not have a hole to pass the wire through the IDC guide.
**If the cable outer diameter is less than 6.3 mm, please use heat shrink tubing or similar to increase the diameter to 6.3-7.2 mm.

△1 Applicable Products List

Product Name	HRS No.
IX30G2-A-10S-CV(7.0)(06)	CL0251-0113-0-06
IX35G2-A-10S-CV(7.0)(06)	CL0251-0101-0-06

HRS DRAWING FOR REFERENCE

DRAWING NO.	EDCX-411766-00-00
PART NO.	IX3*G2-*-*S-CV(7.0)(06)
CODE NO.	CL251
	△1 3/3