

Part No.	Cable color.
~084N1~	White
~084N2~	Black
~084N4~	Blue


NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.

2 Tolerance for 【L】

Length L (mm)	Tolerance (mm)
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3. Specifications are subject to change without notice.


【 DIMENSIONS OF CONNECTOR 】



For stable supply of this series, material supplier of piece part#1 will be changed during 2019-2022. Please note this change in advance. There will be no difference in product performance and quality.

【 PRECAUTIONS FOR HANDLING 】

- ◆ Connector insertion and extraction
 - a. Connector shall be extracted vertically by specialised extraction JIG.
Part No.: H.FL-LP-NCCL Code: CL331-0551-7>
Never hold the cable when extracting the cable because it damages the connector.
 - b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.



1	H.FL75-LP(G)-084	CL331-0808-1	2	1.5 Dia. coaxial cable.
No.	Part No.	Code No.	No.	Part No.

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
			APPROVED :NK. NINOMIYA 20190425 CHECKED :NK. NINOMIYA 20190425 DESIGNED :MK. INOUE 20190425 DRAWN :MK. INOUE 20190425	DRAWING NO. EDC-384937-00-00 PART NO. H.FL75-LPG-084N*-A-L CODE NO. CL321-5111-4-00		