









訂正事項		擔當	檢閱	年月日	訂正事項		擔當	檢閱	年月日
△數	DISCRIPTION OF REVISIONS	B	CHKD	DATE	△數	DISCRIPTION OF REVISIONS	B	CHKD	DATE
△				.	△				.
△				.	△				.
△				.	△				.



NOTE

1. LEAD CO-PLANARITY SHALL BE 0.1mmMAX
2. REEL : 800EA CONNECTORS

3. UL(File No. E132750) AUTHORIZATION ARTICLE.
C-UL(File No. E132750) AUTHORIZATION ARTICLE.



3		COPPER ALLOY	CONTACT AREA : GOLD 0.2mm MIN. SMT LEAD : GOLD 0.05mm MIN. UNDER PLATING : NICKEL 1μm MIN.		C R US				
2		PHOSPHOR BRONZE	Sn PLATED		6	CONNECTOR	KW30-10S-1V		
1		LCP	UL94-V0, BLACK		5	PET	COVER TAPE		
NO.		MATERIAL	FINISH,REMARKS		4	PS	EMBOSS CARRIER TAPE		
					NO.	MATERIAL	FINISH,REMARKS		
CODE NO. (OLD)					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					CHOI 20.06.15 S.W	CHOI 20.06.15 S.W	LIM 20.06.15 S.M	LIM 20.06.15 S.M	
		DRAWING NO.			PART NO.				
SCALE		EDC3-633100			KW30-10S-1V (800)				
UNITS		HRS HIROSE KOREA CO.,LTD.			CODE NO.				
mm					CL 6669-0025-1-800				
					1/				