




Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.





CODE NO.	CONTACT	H	J	K	L	M	N
CL537-0493-0-51	20	16	-	7.5	12	0.38	17.5
CL537-0494-0-51	30	24	-	11.5	12	0.38	25.5
CL537-0495-0-51	36	24	-	11.5	8	0.30	25.5
CL537-0496-0-51	40	24	-	11.5	12	0.38	25.5
CL537-0497-0-51	50	24	-	11.5	8	0.30	25.5
CL537-0498-0-51	60	32	28.4	14.2	12	0.30	33.5



- NOTES 4 1 REEL 1000 CONNECTORS.
- 5 AT THE BEGINNING OF THE REEL, 30 COMPONENTS SHALL BE EMPTY.
AT THE END OF THE REEL, 20 COMPONENTS SHALL BE EMPTY.
- 6 WHEN THE TAPE WIDTH IS 32 mm, SPROCKET HOLES SHALL BE SET ON
BOTH SIDE OF REEL AS SHOWN ON THIS DRAWING.
- 7 PEEL FORCE REFERS TO JIS C 0806(IEC 60286-3) .
- 8 AFTER PACKING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER
CIRCUMFERENCE OF TAPE AND REEL POCKET, AND TAPE DOWN AT THE END THE COLLAR.

HRS	DRAWING NO.	EDC-390684-51-77	
	PART NO.	DF12NB(3.5)-*DP-0.5V(51)	
	CODE NO.	CL537	 