			Ή	1			A 0 11/2		-7 +5	10.17	<u> Д</u>	7
	△の数	訂正記	争	担当	検図	年月日	△の数		記事	担当	検図	年月日
• /\												
\vdash	/ **	m +0 +5					<u>/ \</u>					
	適	用規格						T				
		電源		相	AC • DC	V Hz	重量			500g		
		消費電力 空気源 消費空気量 使用温度範囲						DF51K-	DF51K-30SC(800)		480-0586-0	
				°C~ °C			- -適合端子 -	DF51K-	F51K-30SCA(800)		48	0-0617-0
									•			
ĺ												
7	E 格	区						UL1061 A	AMG30			
ĺ								0210017	111 000			
1							適合電線					
							適合設備					
					性			能				
\vdash		項目			<u> </u>			1,10	規格		ОТ	ΛТ
\vdash			□ +□					网ェレク		- L	QT	AT
	外観、 仕上け	構造および	日倪	、寸法測測	官器にて測	正する		図面と台	致している	ے۔(0	0
1	11 11											
表示			目視	にて確認する。				図面と合致していること			0	0
1	<u></u>								,,,, , , , ,		<u> </u>	<u>`</u> _
1												
1												
144												
構												
1												
造												
<u>`</u> ٔ												
1												
1												
1												
1												
1												
ĺ												
備	考							製図	担当	検図	承認	出図
l	-											
ĺ								設技	設技	設技	設技	
								19.06.24	19.06.24		19.06.25	
-+	F全±日+⁄2 /	りむ獣の無いき	ታ ff全 ナ	:注/+	た海田・	アハス		渡部	渡部	柳澤	荒川	
_		の記載の無い記			を適用し	くしいる。						
小士	QT:確	認試験 AT: 集			用項目				Ta			
注	nc	ヒロセ電機株	式会社	±		4	製品規格	*	製品名			
广 1								407				
<u> </u>		HIROSE ELEC	TRIC	CO.,LTD	١.	4	女中の大竹口・	28	HT	801/DF	51K-30S	S(A)
}	CL CL	HIROSE ELEC	TRIC	CO.,LTD 図番) <u>.</u>	4	製品		НТ	801/DF	51K-30S	S(A)

TO PE