

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO
PE

	COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE	
△						△						
△						△						
APPLICABLE STANDARD												
RATING	ELECTRIC SOURCE	PHASE	AC·DC	V	Hz	WEIGHT	5.0Kg					
	DISSIPATION POWER					APPLICABLE CONNECTOR	3840-1M-18P					
	AIR SOURCE						(CL238-2001-3)					
	AIR CONSUMPTION					APPLICABLE CABLE	φ 5.9CABLE (SWCC SHOWA DEVICE TECHNOLOGY CO., LTD.) IRV-28-18PS					
	OPERATING TEMPERATURE LIMIT	°C ~ °C				APPLICABLE EQUIPMENT	HANDPRESS OS-7					
SPECIFICATIONS												
	ITEM	TEST METHOD				REQUIREMENTS				QT	AT	
CONSTITUTION	APPEARANCE, STRUCTURE AND FINISH	Visually and by measuring instrument.				According to drawing.				○	○	
	MARKING	Confirmed visually.								○	○	
REMARKS						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED		
						Y. KUSABIRAKI 07.11.6	Y. KUSABIRAKI 07.11.6	S.TOYODA 07.11.15	S. Sakai 07.11.15			
Unless otherwise specified, refer to												
Note QT:Qualification Test AT:Assurance Test X:Applicable Test												
HRS HIROSE ELECTRIC CO., LTD.						SPECIFICATION SHEET						PART NO. 3840-1M/CK-MP
CODE NO. (OLD)			DRAWING NO. ELC4-275916			CODE NO. CL902-2146-3			1/1			